


$$3 \leq n \leq 40$$



Technical data:

Housing :PBT (UL94V-0).Black

Terminal:S. Q0.64mm Brass,Gold plating

Current Rating :1Amp Max.

Dielectric Withstanding Voltage:

600V AC R. M. S. for one minute.

Insulation Resistance :5000M ohms Min

AT 500V DC

Contact Resistance :30m ohms Max.

Operating Temperature :-55°C to+105°C

Max Processing Temp :220°C for 10 seconds.

new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY2541WV-N-2xXXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	±0.25
			MODEL NAME	HY2541WV-N-2xXXP		X.x	±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15
FILE.NO.						ANGULAIR	±3