



柄长"H"	Part No. (料号)
12	K9-1267U-R
12	K9-1267U-L

- NOTE:
- 1.Rating:DC30V 0.1A
 - 2.OP:10.70±0.8
 - 3.Operating froce:30±15gf
 - 4.Mechanical Life:3,000,000

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑦	Lever	—	1	Stainless Steel	—	—
⑥	Shrapnel	—	1	Beryllium Copper	—	—
⑤	Contact	—	1	Ag	—	—
④	Terminal	—	3	Brass(0.52t)	Plating silver	—
③	Housing	—	1	PBT	White	—
②	Knob	—	1	PBT	White	—
①	Cover	—	1	PBT	Black	—

APPROVALS		DATE	HRO 韩荣® ELECTRONICS CO.,LTD			
DRAWN	JKUN.LU	2015.4.21	TITLE:	MICRO SWITCHES		
CHECKED			PART NO.	K9-1267U-R		
APPROVALS			TOLERANCES ARE	ANGLE	UNIT: mm	SCALE: 1:1
			30~以下 ±0.30	±2'		
			10~30 ±0.20			
			5~10 ±0.15			
			~ 5 ±0.10			
ECN NO.	REV.	DATE.	CHANGE.	CHECK.	APPRO.	PROJ:

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			