



NOTES:

MATERIAL:

- 1 HOUSING MATERIAL : GLASS FILLED POLYESTER U94V-0.
- 2 CONTACT MATERIAL : PHOSPHOR BRONZE φ0.45mm.
- 3 PLATING : GOLD PLATING OVER NICKEL.
- 4 SHIELD : 0.20mm THICKNESS COPPER ALLOY WITH NICKEL PLATED.

ELECTRICAL:

- 1 VOLTAGE RATING : 125 VAC RMS.
- 2 CURRENT RATING : 15 AMP.
- 3 CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- 4 INSULATION RESISTANCE : 500 MEGOHMS MIN @ 50V DC.
- 5 DIELECTRIC WITHSTANDING RESISTANCE : 1000V AC RMS 50HZ 1MIN.

MECHANICAL:

- 1 DURABILITY : 750 CYCLES MIN.
- 2 PCB RETENTION PRE-SOLDER: 1LB MIN.

ENVIRONMENTAL:

- 1 STORAGE : -40°~+85°
- 2 OPERATION : 0° TO 70°

TOLERANCE TABLE	
	0
±0.30	
±0.20	
±0.05	
	.000

APPROVED:	DATE:	<p>C 深圳市灿科盟实业有限公司 kmtw CHANKLEMENT INDUSTRYCO., LTD</p>
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
ZYJ	2017-02-19	RJ45-8P/8C 弯插 带屏蔽 (脚后3.05)
		PART. NO. R-RJ45R08P-B005
		UNIT mm SCALE Free
		FILE NO. Ckmtw-RJ45-0178 REV. A HY04