



CATEGORY	DESCRIPTION	P/N #
CONNECTOR	MJ45 8P8C SMT H=7.5mm 反口	MJ88-BX11-HRV7-X

料号由原MJ88-BX11-HRV7
 变更为MJ88-BX11-HRV7-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01	—	New Release	XSY	2014.12.25
A02	—	增加包装方式选项	XHY	2017.7.31
A03	—	调整尺寸	LXY	2020.01.07



SPECIFICATIONS:

1. Voltage: 150V AC RMS
2. Current Rating: 1.5A
3. Contact Resistance: 30m Ω MAX.
4. Insulation Resistance: 500MΩ MIN.
5. Dielectric Withstand Voltage :500V AC
6. Operature Temperature: -40°C~80°C
7. Durability: 750 Mating Cycles MIN.



X	Terminal Plating	X	包装方式
0	Au 1u" Plating	C	卷带包装
1	Au 3u" Plating	P	吸塑盒包装
2	Au 6u" Plating		
3	Au 15u" Plating		

Part No.:
 MJ88-BX11-HRV7-X



Recommend PCB Layout
 Jack Top View
 Tolerance: ±0.05mm

C	SHELL	1	BRASS T=0.2mm	Ni PATING	
b	TERMINAL	8	PHOSPHOR BRONZE T=0.3mm	Au/Tin PATING	
a	HOUSING	1	LCP+30%G.F UL94V-0	BLACK	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES	SCALE: 1/1	UNIT: mm	DWG. NO:
DECIMALS: X :±0.5	APPROVED BY	CHECKED BY	PREPARED BY
ANGLES: X :±2°			LXY
X X :±0.3			
X X X :±0.2			

东莞市合陵电子有限公司
 Dongguan Heling Electronic Co.,LTD
 Connector

SIZE: A3 PAGE: 1 OF 1 REV: A03
 APPROVED BY _____ CHECKED BY _____ PREPARED BY LXY
 CUSTOMER COPY