




| | | |
|-----------|----------------|--------------------|
| CATEGORY | DESCRIPTION | P/N # |
| CONNECTOR | RJ45 180度SMT带壳 | MJ882-BX11-H9PS1-P |

由原料号 MJ882-BX11-H9PS1 变更为 MJ882-BX11-H9PS1-X

| REV. | ECN NO | DESCRIPTION | REVISED | DATE |
|------|--------|-------------|---------|------------|
| A01 | | 整理图画 | XSY | 2015.09.15 |
| A02 | | 新增包装选项 | XSY | 2016.05.11 |
| A03 | | 统一塑胶材质 | XSY | 2019.05.02 |




| | |
|---|------------------|
| X | Terminal Plating |
| 0 | Au 1u" Plating |
| 1 | Au 3u" Plating |
| 2 | Au 6u" Plating |
| 3 | Au 15u" Plating |
| 4 | Au 30u" Plating |

| | |
|---|-------|
| X | 包装方式 |
| P | 吸塑盒包装 |



MJ882-BX11-H9PS1-P



Recommend PCB Layout
(Jack Top View)
Tolerance: ±0.05mm

SPECIFICATION

- VOLTAGE RATING: 125 VAC RMS.
- CURRENT RATING: 1.5 AMP
- CONTACT RESISTANCE: 40 mΩ MAX
- INSULATION RESISTANCE: 500MΩ MIN.
- WITHSTAND VOLTAGE: AC1000V RMS 50Hz or 60Hz MIN.
- OPERATING TEMPERATURE: -40°C~+80°C

| NO. | PART NAME | QTY | MATERIAL | PLATING & COLOR | Remark |
|-----|-----------|-----|--------------------------|-----------------|--------|
| e | SHELL | 1 | BRASS T=0.2mm | Ni PALTING | |
| d | ME | 1 | BRASS T=0.35mm | Tin PALTING | |
| c | TERMINAL | 8 | PHOSPHOR BRONZE T=0.35mm | Au/Tin PALTING | |
| b | INSERT | 1 | LCP UJ94V-0 | BLACK | |
| a | HOUSING | 1 | LCP UJ94V-0 | BLACK | |

UNLESS OTHERWISE SPECIFIED TOLERANCES
DECIMALS: ANGLES:
X : ±0.5 X : ±2°
X.X : ±0.3 X.X : ±1°
X.XX : ±0.2

| | | |
|-------------|--------------|-------------|
| SCALE: 1/1 | UNIT: mm | DWG. NO: |
| SIZE: A3 | PAGE: 1 OF 1 | REV: A03 |
| APPROVED BY | CHECKED BY | PREPARED BY |
| DICK | XSY | XSY |

東莞市合陵電子有限公司
DongGuan Heling Electronic Co.,LTD

CUSTOMER COPY