




CATEGORY	DESCRIPTION	P/N #
CONNECTOR	RJ45超薄全包沉板H4-3带灯无内弹	MJ88K-BX11-HXRVLX1-X

REV.	ECN NO	DESCRIPTION	REVISED	DATE
A01		New Release	Luke	2021.09.23



X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating
4	Au 30u" Plating




X	LED-L	LED-R
1	GREEN	YELLOW
2	YELLOW	GREEN
3	ORANGE	GREEN

X	Housing Color
9	PA 9T
L	LCP

MJ88K-BX11-HXRVLX1-X

X	包装方式
C	卷带包装
P	吸塑包装

- NOTE:
1. Voltage: 150V AC RMS
 2. Current Rating: 1.5A
 3. Contact Resistance: 40mΩ MAX.
 4. Insulation Resistance: 500MΩ MIN.
 5. Dielectric Withstand Voltage :500V AC
 6. Operate Temperature: -40°C~80°C
 7. Durability: 750 Mating Cycles MIN.



P.C.B RECOMMENDED HOLE LAYOUT SEEN FROM COMPONENT SIDE.
ALL CENTERLINE DIMENSIONS ARE BASIC

f	LED-R	1	SEE TABLE	Tin PALTING	
e	LED-L	1	SEE TABLE	Tin PALTING	
d	Bottom SHELL	1	SUS T=0.15mm	Ni PALTING	
c	Upper SHELL	1	SUS T=0.2mm	Ni PALTING	
b	TERMINAL	8	PHOSPHOR BRONZE T=0.25mm	Au/Tin PALTING	
a	HOUSING	1	SEE TABLE UL94V-0	BLACK	
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR	Remark

UNLESS OTHERWISE SPECIFIED TOLERANCES:
DECIMALS: ANGLES:
X.X :±0.30 X :±2
X.XX :±0.20 X.X :±1
X.XXX :±0.10

东莞市合陵电子有限公司
 Dongguan Heling Electronic Co.,LTD
 SCALE:1/1 UNIT: mm DWG.NO:
 SIZE: A3 PAGE:1 OF 1 REV:A01
 APPROVED BY: _____ CHECKED BY: _____ PREPARED BY: _____
 DICK: XSY LUK
CUSTOMER COPY