







CATEGORY	DESCRIPTION	P/N #
CONNECTOR	USB 2.0 AF DIP塑壳板插.55	UB21F-XX11-HLRX23-X

REV.	ECN NO.	DESCRIPTION	REVISED	DATE
A01		New Release	XSY	2019-8-8



Tolerance: ± 0.05 Thickness: $1.0 \sim 1.2$ mm
 Recommend PCB Layout
 (Top View)



UB21F-XX11-HLRX23-X

X	Housing Color
B	Black
U	Blue

X	Terminal Plating
0	Au 1u" Plating
1	Au 3u" Plating
2	Au 6u" Plating
3	Au 15u" Plating


X	Shell Material
G	SUS
B	Copper Alloy
S	SPCC

X	包装方式
C	裁带包装
P	吸塑包装

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:

X : ± 0.5 X : $\pm 2^\circ$
 XX : ± 0.3 XX : $\pm 1^\circ$
 XXX : ± 0.2


东莞市合陵电子有限公司
 Dongguan Heling Electronic Co., LTD

SCALE: 1/1 UNIT: mm DWG. NO:

SIZE: A3 PAGE: 1 OF 1 REV: A01

APPROVED BY: TONY CHECKED BY: XSY PREPARED BY: XSY

CUSTOMER COPY

c	Shell	1	See Table T=0.3mm	Ni Plating
b	Terminal	4	Copper Alloy T=0.2mm	See Table
a	Housing	1	LCP UL94V-0	See Table
NO.	PART NAME	QTY	MATERIAL	PLATING & COLOR