



PCB Layout(Pattern side)



Circuit Diagram



Note:
1. Rating: 12V 50mA

NO.1		
PART NO	H	PART NO
A	4.3	O
B	4.5	P
C	5	Q
D	5.5	R
E	6	S
F	6.5	T
G	7	U
H	7.5	V
I	8	W
J	8.5	X
K	9	Y
L	9.5	Z
M	10	1
N	10.5	2

NO.2		
PART NO	vigor	
070	70±30	
100	100±50	
160	160±50	
250	250±50	
320	320±80	
350	350±80	
520	520±130	

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
⑤	Terminal	4	Brass(0.3t)	Plating silver
④	Contact Spring	1	F.Ag/C5210	
③	Base	1	Nylon	Black
②	Cover	1	SPCC/Brass	Plating Sn
①	KNOB	1	Nylon	Black

APPROVALS		DATE	TITLE:	
DRAWN	G.M.Chen	2014/8/18	TACT SWITCHES	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			DEALON 德之隆®	
PART NO.		TD-1212DR-XXH-XXX	SHEET 1 OF 1	
TOLERANCES ARE		SCALE: 1:1	PROJ.	
30 ^{±0.15}	±0.30			
10 ^{±0.10}	±0.20			
5 ^{±0.05}	±0.15			

ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW

CHANGE.	CHECK.	APPRO.