





注: 本板为禁止传输、复制、翻印或传播, 以及用其内容进行复制或传播



| REV | ECN NO. | CONTENT | CHK | DATE |
|-----|---------|---------|-----|------|
| | | | | |


NOTES1:
 UL Standard
 1.Rating voltage/current: 300V//15A
 2.withstanding voltage: AC2000V//1Min
 IEC Standard

| 1. Pollution Degree | 2 |
|--------------------------|-------|
| Overvoltage Category | III |
| Rate Impulse Voltage(KV) | 4.0KV |
| Rate Voltage(V) | 320V |
| Rate Current(A) | 15A |

NOTES2:
 1.Housing: PA66 (UL94V-0)
 2.Solder Pin: Brass (Sn Plated)
 3.Nut: Brass (M2.5)

NOTES3:
 1.Pitch: 5.08mm Poles: 02-24P
 2.Operating temperature: -40℃~+105℃
 3.RoHS Compliance

How to order



| Pitch Range In mm | Nominal Dimension Range In mm | | | | | Nominal Dimension Range | Tolerance |
|-------------------|-------------------------------|---------|---------|---------|---------|-------------------------|-----------|
| | Over 6 | Over 10 | Over 24 | Over 30 | Over 60 | | |
| TO 6 | TO 10 | TO 24 | TO 30 | TO 60 | TO 100 | TO 150 | 0.1/10 |
| ±0.15 | ±0.20 | ±0.30 | ±0.30 | ±0.50 | ±0.70 | ±1.00 | ±2° |

| ITEM | NAME OF PART | NO. OF PART | Q'TY | MATERIAL | NOTE |
|---|--------------|-------------|-------|----------|-----------------------------------|
| DWG | CHK | DATE | UNITS | MM | SHEET/OF |
| APP | DATE | SCALE | 1:1 | A4 | 1/1 |
| CIXI MAIXU ELECTRONICS CO.,LTD 慈溪市迈旭电子有限公司 | | | | | NAME: MX2EDGVM-5.08-XXP DWGNO. |