



注: 本板为禁止运输、复制、翻印文件, 以及用其内容进行交流



REV	ECN NO.	CONTENT	CHK	DATE

NOTES:

- UL Standard
- 1.Rating voltage/current: 300V/8A
- 2.withstanding voltage: AC1600V/1Min
- 3.Torque value: M2.0, 1.77Lbin
- 4.Wire range: 28~16AWG

IEC Standard

Pollution Degree	2	2
Overvoltage Category	III	II
Rate Impulse Voltage(KV)	2.5KV	2.5KV
Rate Voltage(V)	160V	320V
Rate Current(A)	7A	7A

- 2. Torque value: M2, 0.2Nm
- 3. wire range: 15mm<sup>2</sup>

NOTES2:


- 1.Housing: PA66 (UL94V-0)
- 2.Cover: PA66 (UL94V-0)
- 3.Cage: Brass (Ni Plated)
- 4.Conductor: Copper alloy (Sn Plated)
- 5.Screw: Steel (M2.0,Zn Plated)

NOTES3:

- 1.Pitch: 3.81mm Poles: 02-24P
- 2.Stripping length: 7-8mm
- 3.Operating temperature: -40℃~+105℃
- 4.RoHS Compliance

How to order

MX15EDGRK - 381 - XXP - XXXX - XX - X - X



Pitch Range In mm	Nominal Dimension Range				Over 150	Over 1/10
	In mm	Over 30	Over 60	Over 100		
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100	TO 150
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70	±1.00
					±1.30	±2°

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	SCALE	SHEET/OF	1/1
APP	DATE	SCALE	A4		
CIXI MAIXU ELECTRONICS CO.,LTD			MX15EDGRK-3.81-XXP		
慈溪市迈旭电子有限公司			DWGNO.		