






注：本板为禁止运输、复制、编辑文档，以及用其内容进行交流



PCB Layout

Pitch Range		Nominal Dimension		Range	
mm	In	mm	In	mm	In
Over 6	Over 10	Over 30	Over 60	Over 100	Over 150
TO 6	TO 10	TO 24	TO 30	TO 60	TO 100
±0.15	±0.20	±0.30	±0.30	±0.50	±0.70
				±1.00	±1.30
				±2°	

REV	ECN NO.	CONTENT	CHK	DATE

NOTES1:  
 UL Standard  
 1.Rating voltage/current: 300V/20A  
 2.withstanding voltage: AC2000V/1Min  
 3.Torque value: M3, 4,43Lb.in  
 4.Wire range: 26~12AWG  
 IEC Standard

Pollution Degree	Overvoltage Category	Rate Impulse Voltage(kV)	Rate Voltage(V)	Rate Current(A)
3	III	/	250V	/
2	II	/	/	20A

NOTES2:  
 1.Housing: PA66(UL94V-0)  
 2.Solder Pin: Copper alloy(Sn Plated)  
 3.Cage: Brass(Ni Plated)  
 4.Screw: Steel(M3,Zn Plated)

NOTES3:  
 1.Pitch: 5.08mm Poles: 02-24P  
 2.Stripping length: 8mm  
 3.Operating temperature: -40°C~+105°C  
 4.RoHS Compliance

How to order  
 MX129 - 508 - XXX - XXXX - XX - X - X  
 产品型号 间距 极数 颜色: 01:青颜色  
 颜色: GY 橙色:OE 02-99:  
 蓝色:BU 红色:RD 定脚颜色  
 黑色:BK 透明色:TT  
 绿色:GN 黄色:YW  
 透明色:TT 白色:WE

A-Z其他定制  
 0-Y一字螺丝  
 1-S十字螺丝  
 2-P:平头十字螺丝  
 Cu:铜方块  
 Fe:铁方块

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG	CHK	DATE	DATE	UNITS	SCALE
APP	DATE	DATE	SCALE	A4	1/1
CIXI MAIXU ELECTRONICS CO.,LTD			NAME	MX129-5.08-XXX	
慈溪市迈旭电子有限公司			DWGNO.		