



Specifications:

规格:

Voltage rating:600V AC/DC

额定电压: 600V AC/DC

Current rating:9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤10mΩ

接触电阻: ≤10mΩ

After environmental testing:≤20mΩ

环境测试后: ≤20兆欧

9357 W R -2xXX - XX XX
① ② ③ ④ ⑤ ⑥

1. Series No
2. Category:W-wafer
3. Welding Board Angle:R-90
4. Row No.-Pin No: 2xXXPin
5. Material: N0-PA66 94V-0; N2-PA66 94V-7
LP-LCP 94V-0; 6T-PA6T 94V-0; 9T-PA9T94V-0
6. Plating Category: V01:All Gold-Plated Gold Flash;
SN-Bright Tin plating 70u"

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x01	5.60	—	2x07	30.80	25.20
2x02	9.80	4.20	2x08	35.00	29.40
2x03	14.00	8.40	2x09	39.20	33.60
2x04	18.20	12.60	2x10	43.40	37.80
2x05	22.40	16.80	2x11	47.60	42.00
2x06	26.60	21.00	2x12	51.80	46.20

ECN BO.		new		2015/5/3		A		瀚源
DESIGNED		CHECKED		DATE.		REV.		
Mikey		Tom		APPROVAL		DRAWING NUMBER		SCALE: 1/2
				Jerry		PART NAME		SCALE: 3:1
						9357WR-2xXX		UNLESS OTHERWISE
						MODEL NAME		SPECIFIED,TOLERANCE:
						9357WR-2xXX		X. ±0.25
						3RD ANGLE PROJ		X.x ±0.20
						HanElectricity Co.,LTD		X.xx ±0.15
								ANGULAR ±3°
								FILE.NO.