

# KA3501


## PC SMPS Supervisory IC

### Features


- Complete House Keeping Circuit
- Few External Components
- Positive Voltage Protection
- Negative Voltage Protection
- High Current Drive Output for SCR
- Precision Voltage Reference for 5V/12V Outputs
- Power Good Signal Generator with Hysteresis

### Description


The KA3501 is complete housekeeping circuits for use in the secondary side of SMPS(Switched Mode Power Supply). This IC(Integrated Circuit) contains a precision voltage reference, protection circuits and a power good signal generator. It also has a high current drive output for use in conjunction with an external "crowbar" SCR. The reference voltage is trimmed to  $\pm 2\%$  for correct output voltages(+5V/+12V) and power good signal generator is to monitor the voltage level of power good supply for safe operation in a microprocessor circuit. Using the KA3501 requires few external components to accomplish a complete housekeeping circuit for SMPS(Switched Mode Power Supply). The KA3501 is available in an 14-pin DIP.



### Internal Block Diagram



## Pin Assignments



Pin Number	Pin Name	Pin Function Description
1	Vcont	Reference Voltage Control
2	Vref	Precision Reference Voltage
3	Vcc2	+12V Output Voltage
4	Vcc1	+5V Output Voltage
5	Vin2	UVP Input (Negative)
6	Gate	Gate Drive Input for SCR
7	Vcc	Supply Voltage
8	Vin1	PG Input
9	Td	Reference Voltage Delay for PG
10	Timing	PG Delay
11	PG	PG Output
12	Ve	PG Ground (Open Emitter)
13	GND	Ground
14	Feedback	Feedback for Precision Reference

### Absolute Maximum Rating ( Ta = 25°C)

Parameter	Symbol	Value	Unit
Supply Minimum Voltage	Vcc(min)	5	V
Supply Maximum Voltage	Vcc(max)	35	V
UV Input Voltage	Vuv	24	V
Minimum Gate Drive Current	IDR	-25	V
Operating Cathode Current	IK	1 to 30	A
Power Dissipation	Pd	1	W
Operating Temperature Range	Topr	0 to 70	°C

## Electrical Characteristic

(Refer to the test circuit ,  $V_{CC}=20V$ ,  $T_a=25^{\circ}C$ , unless otherwise stated)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Temperature Stability for $V_{REF}$	$\Delta V_{REF}$	-	-	17	-	mV
<b>PROTECTION SECTION</b>						
Positive Protection Voltage	$V_{POSI}$	-	5.7	6.0	6.4	V
Negative Protection Voltage	$V_{NEGA}$	$V_{CC1} = 5V$	-1.5	-2.5	-3.5	V
Negative Input Resistor	$R_{NEGA}$	Pin 4 to Pin 5	8.5	10	11.5	k $\Omega$
Gate Drive Current	$I_{DR}$	$V_{GATE} = 0.7 V$	-25	-50	-	V
<b>REFERENCE SECTION</b>						
Reference Input Voltage	$V_{REF}$	$I_K = 10mA$	2.44	2.50	2.56	V
Current Stability	$\Delta V_{REF}$	$I_K=1mA$ to 10mA	-	5	20	mV
Absolute Precision of Internal Three Resistors	$R_{int}$	-	-	-	$\pm 20$	%
Relative Deviation of Three Resistors	$R_{rate}$	-	-	$\pm 0.5$	$\pm 3$	%
Temperature Stability (Note1)	$\Delta V_{REF}$	$T_a = 0$ to $70^{\circ}C$	-	13	17	mV
Gain Bandwidth (Note1)	GBW	$GV = 1$	-	1	-	MHz
<b>POWER GOOD SECTION</b>						
Detecting Input Voltage	$V_{IN1}$	-	1.23	1.28	1.33	V
Detecting PG Voltage	$V_{DET}$	-	4.1	4.3	4.5	V
Hysteresis Voltage 1	$HY1$	-	10	20	40	mV
Hysteresis Voltage 2	$HY2$	-	200	250	-	mV
Charging Current for PG Delay	$I_{CHG}$	-	-8	-14	-20	$\mu A$
PG Output Resistor	$R_{PG}$	-	7.7	9.0	10.3	k $\Omega$
PG Output Saturation Voltage	$V_{SAT}$	$I_{SINK} = 6mA$	-	0.2	0.4	V
PG Output Leakage Current	$I_{O(LKG)}$	-	-	0.01	1	$\mu A$
<b>TOTAL STANDBY CURRENT</b>						
Supply Current	$I_{CC}$	$V_{CC} = 20V$ , $V_{CC1} = 5V$	-	3	5	mA

**Note:**


1. These parameters, although guaranteed, are not 100% tested in production

# Mechanical Dimensions

## Package

Dimensions in millimeters

### 14-DIP



---

## Ordering Information

Product Number	Package	Operating Temperature
KA3501	14-DIP	0°C ~ +70°C

**DISCLAIMER**

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

**LIFE SUPPORT POLICY**

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.