

HIGH-SPEED SWITCHING DIODES

Item	V _{RM} (V) I _o (A)	30~40	50~60	70~80	90~100	200~300	300~400	t _{tr} (ns)	C (pF)	Remarks
DHD	0.12	DS442						4	3	
	0.13		DS442X					2	2	
	0.20				DS446			4	3	
	0.10	DS441						-	6	Low leakage current
Mini DHD	0.12		GMA01		GMA01U			4	3	
		GMB01L	GMB01					4	3	
Leadless	0.15		LFB01L		LFB01			4	3	
CP	0.10			DSA010				4	4	
				DSC010				4	4	
				DSB010				4	3	
				DSD010				4	3	
	0.15			DCA010				4	4	2-element center tap (anode common)
				DCB010				4	3	2-element center tap (cathode common)
				DCC010				4	3	2-element series connection
				DSA015				8	9	
SPA	0.15			DSB015				5	7	
				DCA015				8	9	2-element center tap (anode common)
				DCB015				5	7	2-element center tap (cathode common)
CP4	0.10			DCD015				15	9	2-element center tap (anode common)
				DCE015				12	7	2-element center tap (cathode common)
MCP	0.10			DWA010		DWC010		4	2	2-element separate type
MCP	0.10		◎DCF010					4	4	2-element center tap (anode common)
			◎DCG010					4	3	2-element center tap (cathode common)

ZENER DIODES

P(W)	2 3 4 5 6 7 8 9 10 11 12 14 15 16 18 20 22 24 27 30 33 36 39 43 47 51	Package
0.2	DZD2.0X~DZD24Z	CP
0.4	GZS2.0X~GZS39R	Mini DHD
0.5	GZA2.0X~GZA51Z	DHD(DO-35)
1.0	GZB2.0B~GZB36C	DHD
1.0	DZB6.2~DZB30	Plastic