




Dept	
Qty	
DC	1
ED	1
IE	1
ISO	1
PD	1
R&D	1
SD	1
QA	1
QC	1
QF	1

The information provided herein is from CONNPLY Electronic Co., Ltd. and is confidential. Any disclosure to a party other than the recipient is prohibited. The intellectual properties and its rights contained herein, including but not limited to, trademarks, patents, copyrights, trade secrets, and technical know-how, are owned exclusively by CONNPLY or its affiliates. Unauthorized use or reproduction of any part of this document is strictly prohibited. CONNPLY may enforce its intellectual property rights at its own discretion, failures or delays to exercise such rights does not constitute a waiver of such rights.

A&B&C: Customer length available  
N: Number of contacts/2



(Series Image-Reference Only)




Table A

Type	Dimension			Pin Length
	A	B	C	
1	4.00	2.80	9.30	10.50 14.50
2	6.00	2.80	11.30	12.50 16.50
3	2.42	5.00	12.70	16.00 20.00
4	3.70	3.00	9.00	10.50 14.50
5	3.20	3.00	9.20	10.50 14.50
6	8.00	2.80	13.30	14.50 18.50
7	3.50	3.00	9.25	10.50 14.50
8	4.00	4.00	9.30	11.70 15.70

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION		TITLE	2.00mm Pin Header
X.	±0.60	X.	±5°	UNITS	mm	Double Row R/A Type	
.X	±0.38	.X	±3°	SHEET SIZE	A4	SERIES	DS1025-06 SERIES
.XX	±0.25	.XX	±2°				
DRAWING TYPE		CUSTOMER					
SCALE		1:1	SHEET	1 OF 1			
DRAWING NO.		C-DS1025-06-XXXXX-X-E					

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 05/08/05'		LJC 05/08/05'
E	DRAWING UPDATE	JLZ 06/18/19'		

Notes:

Specifications:

- Contact Resistance: 20mΩ Max.
- Insulation Resistance: 1000MΩ Min.
- Dielectric Withstanding Voltage: 500V AC(rms) For 1 Minute.
- Current Rating:1.5A.
- Temperature: -40°C~+105°C.

Materials:

- Contact Material: Copper Alloy.
- Contact Plating: Gold Plating Over Nickel.
- Insulator Material: PA-9T,Black,UL94-V0.

Product Number Code:

DS1025-06 - X X X X X X - X

- Plating level  
3A:Level 3A B:Level B
- Dim A/B/C type  
1:Type 1  
2:Type 2  
A\*-\*B\*-\*C\*\*  
.....
- Contacts type  
R:R/A Type
- Housing color  
B:Black
- Contact plating  
8: Full gold flash
- Connector type  
P:Plug
- No.of contacts  
2x2-2x40

**晨翔电子有限公司**  
CONNPLY ELECTRONIC CO. LTD