

SPECIFICATIONS

Current Rating: 3Amp  
 Insulator resistance: 5000MΩ min.  
 Dielectric Withstanding: 600AC/DC  
 Operating Temperature: -40° ~ +105° C  
 Contact Material: Brass  
 Insulator Material: PBT

UNSPECIFIED TOLERANCE: ±0.20

Dimen Sions List

Contacts Per row	Dimensions		Contacts Per row	Dimensions	
	A	B		A	B
1	2.54	0	21	53.34	50.80
2	5.08	2.54	22	55.88	53.34
3	7.62	5.08	23	58.42	55.88
4	10.16	7.62	24	60.96	58.42
5	12.70	10.16	25	63.50	60.96
6	15.24	12.70	26	66.04	63.50
7	17.78	15.24	27	68.58	66.04
8	20.32	17.78	28	71.12	68.58
9	22.86	20.32	29	73.66	71.12
10	25.40	22.86	30	76.20	73.66
11	27.94	25.40	31	78.74	76.20
12	30.48	27.94	32	81.28	78.74
13	33.02	30.48	33	83.82	81.28
14	35.56	33.02	34	86.36	83.82
15	38.10	35.56	35	88.90	86.36
16	40.64	38.10	36	91.44	88.90
17	43.18	40.64	37	93.98	91.44
18	45.72	43.18	38	96.52	93.98
19	48.26	45.72	39	99.06	96.52
20	50.80	48.26	40	101.6	99.06

深圳市连欣科技有限公司

http://www.szlianxinkeji.com/

PITCH2.54mm 180° 2\*NP 排针

Customer:

Approval:

Unit


Date

Drawing No:

Check:

mm

11.11.04



P/NO: XDHM-0254\*\*H-02\*\*P

Pin Longer:

Signatuer: