






REV	LTR	DESCRIPTION	DATE	APPROVED



建议P.C.B LAYOUT

- 规格说明: Specifications:
- 电气特性: Electrical:
- 额定电流: Current Rating 1.0A/contact terminal
 - 额定电压: Voltage Rating 30V DC
 - 接触电阻: Contact Resistance 30 milliohms MAX
 - 绝缘电压: Dielectric Withstanding Voltage: 300 V AC AT Sea Level
 - 绝缘电阻: Insulation Resistance: 1000MEGA ohms MIN
- 物理性能: Mechanical:
- 插拔力: Connector Mate and Unmate Force
Mate force: 3.0kgf(MAX)
Unmate force: 0.7kgf(MIN)
 - 端子保持力: Terminal Retention 1.2kgf(MIN)
- 原材料: Material:
- 壳体: Housing: Hing Temperature Ternmaplastics, UI P A 6 PBT White/Black
 - 端子: Contact: Copper Alloy C5191/C2680
 - 外壳: Shell: Copper Alloy SPCC/C2680
- 电镀: Finish:
- 端子: Contact: Plated Gold in Mating Area; Tin On Solder Talls
 - 外壳: Shell: Nickel Plating

公差一律表 TOLERANCE UNLESS OTHERWISE		深圳市连欣科技有限公司									
.X±0.2	X.±5'	??	DATE	DATE	UNIT	MM	NAME:	PART NO.	XXX-0421-10		
XX±0.05	.X±2'	??	CHECKED	CHECKED	SCALE	1:1	设计	LIUFU	DWG NO.		
XXX±0.02	.XX±1'	??	APPROVE	APPROVE	角法	VIEW	制图	版本	AO	页数	PG1
							DRAWING	DRAWING	VER	SHEET	