

Notes:

1.Materials:

Housing:Thermoplastic,UL94V-0,Color is black.
Terminal:Phosphor Bronze.
Shell:Stainless








2.Plating:

Terminal:Gold flash on contact area.
Matte tin 80u" on solder tails.
Nickel 50u" underplated over all.
Shell:Nickel 50u" plated over all.

3.LED plated:

DIP solder plating:Matte tin 100u" on all.

4.Mylar:Clear polyester.



Recomend PCB Layout

- Tolerance:±0.05mm (Top view)
1.Recomended PCB layout thickness:1.20±0.05
2.Processing temperature should not exceed 260 centigrade.

LED electrical characteristic			
Node	Color		
A1(+)	A2(-)	Yellow	A1- A2
B1(+)	B2(-)	Green	B1- B2

General Tolerances			深圳市连欣科技有限公司				
LINEAR	0.0	±0.25	ANGLES	±1.5°			
	0.00	±0.15		TITLE: RJ45 LED Socket DIP/双模式/9.8mm			
A4	NAME	DATE	PART NO. XJRJ-0324-022				
APPROVED							
DESIGNER							
DRAWN	Danny Lai 6/6/2012						
REV.	REVISION RECORD	ECN	DATE	UNIT	SCALE	REV.	PAGE
				MM	1:1	A	2/2

REV.	REVISION RECORD	ECN	DATE