







客戶版

REV.	ECN NDL	DESCRIPTION	DRAW	CHECK	APPD.	DATE
A0	N/A	NEW	DEANSHEN	\	JASTIN	2014.10.20



SPECIFICATIONS:
 Contact current Rating:
 1.5 Amperes
 Dielectric Withstanding Voltage: AC 150V(RMS)
 Insulation resistance: 1000 Megohms Minimum.
 Contact Resistance:
 30mΩ Max
 50mΩ Max for other contacts
 Mechanical Characteristics:
 Mating Force: 35 Newtons. Maximum
 Unmating Force: 10 Newtons. Minimum.

3	FORK	2	C2601R-H T=0.25 Contact Plating Au, Solder Area Matte Sn
2	CONTACT1	22	C5191R-H T=0.25 Contact Plating Au, Solder Area Matte Sn
1	HOUSING	1	LCP +30%G.F. BLACK UL94V-0

深圳市连欣科技有限公司

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				DRAFT WHERE APPLICABLE	DRAWN BY DATE
	MM	INCH	APPROX.	APPROX.		Dean Oct.20.2017
▽0	.X ±0.35	.X ±0.15	±	±	MUST REMAIN WITHIN DIMENSIONS	CHECKED BY DATE
▽0.05	.XX ±0.25	.XX ±0.10	±	±		APPROVED BY DATE
▽0.1	.XXX ±0.15	.XXX ±0.05	±	±		
	ANGULAR ±1°					

TITLE:		CUSTOMER COPY	
SATA 7+15P F 板下 H5.0 SMT			
THIRD ANGLE PROJECTION	PART NO.	DWG NO.	SHEET NO.
	XJTS-2205-0531	SATA2205-0531	1/1