






REV	DESCRIPTION	APPD	DATE


- NOTES:
- MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V_0.COLOR:BLACK
CONTACT: COPPER ALLOYS.
COVER: COPPER ALLOYS OR STEEL.
 - PLATING:
UNDERPLATE: NICKEL.
CONTACT AREA: GOLD OVER NICKEL.
SOLDER AREA: TIN OVER NICKEL.
 - MULTIMEDIA CARD COMPATIBLE





PIN NO.	NAME
PIN 1	VCC
PIN 2	GND
PIN 3	RST
PIN 4	VPP
PIN 5	CLK
PIN 6	I/O
PIN 7	DATO
PIN 8	MCMD
PIN 9	CARD DETECT Switch
PIN 10	GND




DWG NO.: SMPXX-SI1-2000-A	MATERIAL:	深圳市连欣科技有限公司	
LOT NO.: XXX	FINISH:	SIM PUSH-PUSH卡座 1.9H	
UNIT: mm	SIZE: A4	PART NO	REV: C/0
TOLERANCES: GENERAL ANGLE: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15		CHK: 杨 俊 922711	SCALE: 1:1
DR: 杨 俊 922711		APP:	SHEET: 1 OF 2







NO. 1




纸箱规格: 350*350*385

NO. 4



NO. 3



NO. 2

1. 材质要求:

- 1.1 纸箱的材质为K=K; 外形尺寸为35*35*38.5;
- 1.2 卷盘的材质为PS, 卷盘的外形尺寸为 ϕ 330*30.4;
- 1.3 卷带的材质为PS, 卷带的外形尺寸为20200*24.00*3.0mm;

2. 包装方式:

- 2.1 将卷带放入包装机后, 前空5PCS, 后放产品500PCS, 再后空5PCS; 上带留200mm长度。
- 2.2 将包装好的产品从包装机上取下并包装好, 贴上内盘标签;
- 2.3 把累叠好的7盘叠放入纸箱中共计4.9Kset1, 上下放纸板, 纸箱四个角塞护角纸;
- 2.4 把包装好的成品打包邮箱, 并在纸箱外贴上标签

REV	DESCRIPTION	APPD	DATE

深圳市连欣科技有限公司

DWG NO: SMPXX-SIS1-2000-A	MATERIAL:	TITLE: SIM PUSH-PUSH卡座 1.9H	
LOT NO: XXXX	FINISH:	PART NO: XDMS-08A1-094	REV: C/0
UNIT: mm	SIZE: A4	SCALE: 1:1	SHEET: 2 OF 2
TOLERANCES: GENERAL		DR: 杨俊 09/13	APP:
X.X=±0.35	ANGLE: X.X=±3.0°	CHK:	
X.XX=±0.25	X.XX=±2.0°	APP:	
X.XXX=±0.15			