

Technical Data

Material



Contact Material: Brass/Phosphor Bronze
 Contact plating: Nicker/Gold Flash
 Insulator Material: Black Polyester UL94V-0
 Standard: PBT+30%G F

Electrical

Current rating: 3.0Amps/contact max
 Contact resistance: $\leq 20\text{m}\Omega$ / contact
 Insulation resistance: $\geq 1000\text{M}\Omega$ at V=100V
 Withstanding Voltage: 1000V AC/minute

Mechanical

Operaing temperature: -40 C to+105C



HY-2541-A 1 X X

HOUSING COLOR:
 B:BLACK BL:BLUE Y:YELLOW
 W:WHITE GR:GREEN R:RED

CONTACT PLATING:
 GF:FULL GOLD FLASH
 NI:NICKEL
 GN:GOLD+NICKEL

HEIGHT:
 1:13.50mm

HOUSING TYPE:
 A:OPEN B:CLOSE C:LONG

		new		2015/5/3	A	瀚源	
ECN BO.		DESCRIPTION.		DATE.	REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY-2541-A1XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.	± 0.25
			MODEL NAME	HY-2541-A1XX		X.x	± 0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	± 0.15
						ANGULAR	$\pm 3^\circ$
					FILE.NO.		