



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000 AC/minute
- 7、Material:Nylon66, UL94V-0

编 号	尺寸 (mm)	
	A	B
A2504-02Y	2.50	6.80
A2504-03Y	5.00	9.30
A2504-04Y	7.50	11.80
A2504-05Y	10.00	14.30
A2504-06Y	12.50	16.80
A2504-07Y	15.00	19.30
A2504-08Y	17.50	21.80
A2504-09Y	20.00	24.30
A2504-10Y	22.50	26.80
A2504-11Y	25.00	29.30
A2504-12Y	27.50	31.80
A2504-20Y	47.50	59.30

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	A2504-NY		版本 REV.	A	
			X.±0.25	X.*±2'		2013、07、01	品名 TITLE		HA孔座	页次 SHEET			1/1
			.X±0.20	.X'±1'		2013、07、03	客户料号 CUTM. NO.						
			.XX±0.15	.XX'±0.5'		核 准 APPROVAL	张名		深圳市金航标电子有限公司				www.kinghelm.com.cn
.XXX±0.10	.XXX'±0.5'	单 位 UNITS	MM	比 例 SCALE	1:1	KH-A2504-02Y		0755-28190160					