



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
A2504-R-02AWD	2.50	7.50
A2504-R-03AWD	5.00	10.00
A2504-R-04AWD	7.50	12.50
A2504-R-05AWD	10.00	15.00
A2504-R-06AWD	12.50	17.50
A2504-R-07AWD	15.00	20.00
A2504-R-08AWD	17.50	22.50
A2504-R-09AWD	20.00	25.00
A2504-R-10AWD	22.50	27.50
A2504-R-11AWD	25.00	30.00
A2504-R-12AWD	27.50	32.50
A2504-R-20AWD	47.50	52.50

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENEAL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	A2504-R-NAWD		版本 REV.	A
			X.±0.25	X.*±2'		2021、05、03		品名 TITLE	HA定位弯针 WAFER DIP TYPE		页次 SHEET	1/1
			.X±0.20	.X*±1'	审核 CHECK	2021、05、04	张名	客户料号 CUTM. NO.				
			.XX±0.15	.XX*±0.5'	核准 APPROVAL	2021、05、05	张名	深圳市金航标电子有限公司		www.kinghelm.com.cn		
			.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1	KH-A2504-R-05AWD		0755-28190160	