


**Kinghelm®**

| REVISIONS |        |             |     |     |      |
|-----------|--------|-------------|-----|-----|------|
| REV       | NUMBER | DESCRIPTION | DWN | CHK | DATE |
| A         |        | DESIGN      |     |     |      |
|           |        |             |     |     |      |



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DC 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES.
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION            | QTY. |
|----------|-------------|------------------------|------|
| ③        | 套管          | OD:2.5* 15 mm 套管       | 1    |
| ②        | 接头          | SMA 公头直头,公针,镀金         | 1    |
| ①        | 同轴线         | RG1.78棕色同轴线, OD:1.78mm | AS   |

**深圳市金航标电子有限公司**  
**SHENZHEN KINGHELM ELECTRON CO., LTD.**

|                                  |  |           |                                      |
|----------------------------------|--|-----------|--------------------------------------|
| ALL DIMENSION ARE IN MM          | DRI  | DATE      | KH-SMAJ-221-RG1.37-80                |
|                                  | DRAIN. Jamy  | 2023/8/11 |                                      |
| COMPUTER GENERATED IN SOLIDWORKS | CHK. Alan  | 2023/8/11 |                                      |
| DO NOT SCALE THIS DRAWING        | APP. Ellis   | 2023/8/11 |                                      |
| PROJECTION                       | GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX<br>± 1° ± 0.3 ± 0.25 ± 0.150 |           | www.kinghelm.com.cn<br>0755-28190160 |
|                                  | SCALE: Free  | TYPE      |                                      |