



MICROCIRCUIT DATA SHEET

MV54ACTQ245-X REV 0A0

Original Creation Date: 04/10/97
 Last Update Date: 08/18/99
 Last Major Revision Date: 04/10/97

Octal Bidirectional Transceiver With 3-State Inputs/Outputs

General Description

The ACQ/ACTQ245 contains eight non-inverting bidirectional buffers with TRI-STATE outputs and is intended for bus-oriented applications. Current sinking capability is 24 mA at both the A and B ports. The Transmit/Receiver (T/ \bar{R}) input determines the direction of data flow through the bidirectional transceiver. Transmit (Active-HIGH) enables data from A ports to B ports; Receive (active-LOW) enables data from B ports to A ports. The Output Enable input, when HIGH, disables both A and B ports by placing them in a HIGH Z condition.

The ACQ/ACTQ utilizes NSC Quiet Series technology to guarantee quiet output switching and improve dynamic threshold performance. FACT Quiet Series TM features GTO TM output control and undershoot corrector in addition to a split ground bus for superior performance.

Industry Part Number

54ACTQ245

Prime Die

D245

NS Part Numbers

54ACTQ245E-QMLV*
 54ACTQ245ERQMLV*
 54ACTQ245J-QMLV**
 54ACTQ245JRQMLV**
 54ACTQ245W-QMLV***
 54ACTQ245WRQMLV***

Controlling Document

5962-92187

Processing

MIL-STD-883, Method 5004

Quality Conformance Inspection

MIL-STD-883 5005

Subgrp	Description	Temp (°C)
1	Static tests at	+25 C
2	Static tests at	+125 C
3	Static tests at	-55 C
4	Dynamic tests at	+25 C
5	Dynamic tests at	+125 C
6	Dynamic tests at	-55 C
7	Functional tests at	+25 C
8A	Functional tests at	+125 C
8B	Functional tests at	-55 C
9	Switching tests at	+25 C
10	Switching tests at	+125 C
11	Switching tests at	-55 C

Features

- Guaranteed simultaneous switching noise level and dynamic threshold performance
- Improved latch-up immunity
- TRI-STATE outputs drive bus lines or buffer memory address registers
- Outputs source/sink 24 mA
- Standard Military Drawing (SMD)
 - ACTQ245: 5962-9218701V2A*, VRA**, VSA***
 - ACTQ245: 5962R9218701V2A*, VRA**, VSA***

(Absolute Maximum Ratings)

(Note 1)

Supply Voltage (Vcc)	-0.5V to +7.0V
DC Input Diode Current (Iik)	
Vi = -0.5V	-20 mA
Vi = Vcc +0.5V	+20 mA
DC Input Voltage (Vi)	-0.5V to Vcc +0.5V
DC Output Diode Current (Iok)	
Vo = -0.5V	-20 mA
Vo = Vcc +0.5V	+20 mA
DC Output Voltage (Vo)	-0.5V to Vcc +0.5V
DC Output Source or Sink Current (Io)	±50 mA
DC Vcc or Ground Current per Output Pin (Icc or Ignd)	±50 mA
Storage Temperature (Tstg)	-65 C to +150 C
DC Latch-Up Source or Sink Current	±300 mA
Junction Temperature (Tj)	
CDIP	175 C

Note 1: Absolute maximum ratings are those values beyond which damage to the device may occur. The databook specifications should be met, without exception, to ensure that the system design is reliable over its power supply, temperature, and output/input loading variables. National does not recommend operation of FACT™ circuits outside databook specifications.

Recommended Operating Conditions

Supply Voltage (Vcc)	4.5V to 5.5V
Input Voltage (Vi)	0V to Vcc
Output Voltage (Vo)	0V to Vcc
Operating Temperature	-55 C to +125 C
Minimum Input Edge Rate (Delta V/Delta t)	
ACTQ Devices	
Vin from 0.8V to 2.0V	
Vcc @ 4.5V, 5.5V	125 mV/ns

Electrical Characteristics

DC PARAMETERS

(The following conditions apply to all the following parameters, unless otherwise specified.)
DC: VCC 4.5V to 5.5V, Temp. Range: -55C to 125C.

SYMBOL	PARAMETER	CONDITIONS	NOTES	PIN-NAME	MIN	MAX	UNIT	SUB-GROUPS
IIH	High Level Input Current	VCC=5.5V, VM=5.5V	1, 2	INPUT		0.1	uA	1
			1, 2	INPUT		1.0	uA	2, 3
IIL	Low Level Input Current	VCC=5.5V, VM=0.0V	1, 2	INPUT		-0.1	uA	1
			1, 2	INPUT		-1.0	uA	2, 3
VOL	Low level output voltage	VCC=4.5V, VIL=0.8V, IOL=50.0uA	1, 2	OUTPUT		.10	V	1, 2, 3
		VCC=5.5V, VIL=0.8V, IOL=50.0uA	1, 2	OUTPUT		.10	V	1, 2, 3
		VCC=4.5V, VIL=0.8V, IOL=24.0mA	1, 2	OUTPUT		.36	V	1
			1, 2	OUTPUT		.50	V	2, 3
		VCC=5.5V, VIL=0.8V, IOL=24.0mA	1, 2	OUTPUT		.36	V	1
			1, 2	OUTPUT		.50	V	2, 3
VIOL	Dynamic Output Current LOW	VCC=5.5V, VIH=5.5V, VIL=0.0V, IOL=50.0mA	1, 2, 5	OUTPUT		1.65	V	1, 2, 3
VOH	High Level Output Voltage	VCC=4.5V, VIH=2.0V, VIL=0.8V, IOH=-50.0uA	1, 2	OUTPUT	4.40		V	1, 2, 3
		VCC=5.5V, VIH=2.0V, VIL=0.8V, IOH=-50.0uA	1, 2	OUTPUT	5.40		V	1, 2, 3
		VCC=4.5V, VIH=2.0V, VIL=0.8V, IOH=-24.0mA	1, 2	OUTPUT	3.86		V	1
			1, 2	OUTPUT	3.70		V	2, 3
		VCC=5.5V, VIH=2.0V, VIL=0.8V, IOH=-24mA	1, 2	OUTPUT	4.86		V	1
			1, 2	OUTPUT	4.70		V	2, 3
VIOH	Dynamic Output Current HIGH	VCC=5.5V, VIH=5.5V, VIL=0.0V, IOH=-50.0mA	1, 2, 5	OUTPUT	3.85		V	1, 2, 3
IOZH	Maximum TRI-STATE Leakage Current	VCC=4.5V, VM=4.5V, VINL=0.0V, VIH=2.0V	1, 2	OUTPUT		0.25	uA	1
			1, 2	OUTPUT		5.0	uA	2, 3
		VCC=5.5V, VM=5.5V, VINL=0.0V, VIH=2.0V	1, 2	OUTPUT		0.25	uA	1
			1, 2	OUTPUT		5.0	uA	2, 3
IOZL	Maximum TRI-STATE Leakage Current	VCC=4.5V, VM=0.0V, VINH=4.5V, VIH=2.0V	1, 2	OUTPUT		-0.25	uA	1
			1, 2	OUTPUT		-5.0	uA	2, 3
		VCC=5.5V, VM=0.0V, VINH=5.5V, VIH=2.0V	1, 2	OUTPUT		-0.25	uA	1
			1, 2	OUTPUT		-5.0	uA	2, 3

Electrical Characteristics

DC PARAMETERS (Continued)

(The following conditions apply to all the following parameters, unless otherwise specified.)
DC: VCC 4.5V to 5.5V, Temp. Range: -55C to 125C.

SYMBOL	PARAMETER	CONDITIONS	NOTES	PIN-NAME	MIN	MAX	UNIT	SUB-GROUPS
ICCH	Supply Current	VCC=5.5V, VINH=5.5, VINL=0.0V	1, 2	VCC		100	nA	1
			1, 2	VCC		80	uA	2, 3
ICCL	Supply Current	VCC=5.5V, VINL=0.0V	1, 2	VCC		100	nA	1
			1, 2	VCC		80	uA	2, 3
IC CZ	Supply Current	VCC=5.5V, VINH=5.5V, VINL=0.0V	1, 2	VCC		100	nA	1
			1, 2	VCC		80	uA	2, 3
ICCF	Supply Current Functional	VCC=5.5V, VINH=5.5V, VINL=0.0V	1, 2	VCC		100	nA	1
			1, 2	VCC		80	uA	2, 3
ICCT	Supply Current	VCC=5.5V, VINT=VCC-2.1V	1, 2	VCC		1.0	mA	1
			1, 2	VCC		1.6	mA	2, 3
VIKL	Negative Input Clamp Voltage	VCC=4.5V, IKL=-18mA	1, 2	INPUT		-1.2	V	1, 2, 3
VIKH	Positive Input Clamp Voltage	VCC=4.5V, IKL= 18mA	1, 2	INPUT		5.7	V	1, 2, 3
VILD	Maximum Low Level Dynamic Input Voltage	VCC=5.0V, LOAD 50pF / 500 OHMS	6, 9	INPUT		0.8	V	4
VIHD	Minimum High Level Dynamic Input Voltage	VCC=5.0V, LOAD 50pF / 500 OHMS	6, 9	INPUT	2.2		V	4
VOLP	Quiet Output Maximum Dynamic VOL	VCC=5.0V, LOAD 50pF / 500 OHMS	6, 8	OUTPUT		1.65	V	4
VOLV	Quiet Output Minimum Dynamic VOL	VCC=5.0V, LOAD 50pF / 500 OHMS	6, 8	OUTPUT		-1.2	V	4

Electrical Characteristics

AC PARAMETERS

(The following conditions apply to all the following parameters, unless otherwise specified.)
AC: CL=50pf, RL=500 OHMS, TR/TF=3.0ns, Temp range: -55C to +125C.

SYMBOL	PARAMETER	CONDITIONS	NOTES	PIN-NAME	MIN	MAX	UNIT	SUB-GROUPS
tpLH	Propagation Delay	VCC=4.5V	3, 4, 7	An/Bn or Bn/An	1.5	8.0	ns	9
			3, 4, 7	An/Bn or Bn/An	1.5	9.0	ns	10, 11
tpHL	Propagation Delay	VCC=4.5V	3, 4, 7	An/Bn or Bn/An	1.5	8.0	ns	9
			3, 4, 7	An/Bn or Bn/An	1.5	9.0	ns	10, 11
tpZL	Output Enable Time	VCC=4.5V	3, 4, 7	\overline{OE} to An or Bn	1.5	11.0	ns	9
			3, 4, 7	\overline{OE} to An or Bn	1.5	12.0	ns	10, 11
tpZH	Output Enable Time	VCC=4.5V	3, 4, 7	\overline{OE} to An or Bn	1.5	11.0	ns	9
			3, 4, 7	\overline{OE} to An or Bn	1.5	12.0	ns	10, 11
tpHZ	Output Disable Time	VCC=4.5V	3, 4, 7	\overline{OE} to An or Bn	1.5	10.0	ns	9
			3, 4, 7	\overline{OE} to An or Bn	1.5	11.5	ns	10, 11
tpLZ	Output Disable Time	VCC=4.5V	3, 4, 7	\overline{OE} to An or Bn	1.5	10.0	ns	9
			3, 4, 7	\overline{OE} to An or Bn	1.5	11.5	ns	10, 11

Note 1: SCREEN TESTED 100% ON EACH DEVICE AT +25C, +125C & -55C TEMPERATURE, SUBGROUPS 1, 2, 3, 7, & 8.

Note 2: SAMPLE TESTED (METHOD 5005, TABLE 1) ON EACH MFG. LOT AT +25C, +125C & -55C TEMPERATURE, SUBGROUPS A1, 2, 3, 7, & 8.

Note 3: SCREEN TESTED 100% ON EACH DEVICE AT +25C TEMPERATURE ONLY SUBGROUP A9.

Note 4: SAMPLE TESTED (METHOD 5005, TABLE 1) ON EACH MFG. LOT AT +25C, +125C & -55C TEMPERATURE, SUBGROUPS A9, 10 & 11.

Note 5: TRANSMISSION LINE DRIVING TEST, GUARDBANDED LIMITS SET FOR +25C, 2 MSEC DURATION MAX.

Note 6: GUARANTEED BUT NOT TESTED. (DESIGN CHARACTERIZATION DATA)

(Continued)

- Note 7: +25C, +125C & -55C MIN LIMITS GUARANTEED FOR 5.5V BY GUARDBANDING 4.5V MINIMUM LIMITS.
- Note 8: MAX NUMBER OF OUTPUTS DEFINED AS (N). DATA INPUTS ARE DRIVEN 0V TO 3V. ONE OUTPUT @ VOL.
- Note 9: MAX NUMBER OF DATA INPUTS (N) SWITCHING. (N-1) INPUTS SWITCHING 0V TO 3V. INPUT-UNDER-TEST SWITCHING 3V TO THRESHOLD (VILD), 0V TO THRESHOLD (VIHD), FREQ= 1 MHZ.

Revision History

Rev	ECN #	Rel Date	Originator	Changes
0A0	M0003378	08/18/99	Linda Collins	Initial MDS Release