



P.C.B LAYOUT

Specifications:
 规格:
 Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage: 1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range: -40°C ~ +105°C
 温度范围: -40°C ~ +105°C
 Insulation resistance: ≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance: ≤20mΩ
 接触电阻: ≤20mΩ
 Material: PA6T UL94V-0
 材质: PA6T UL94V-0
 Plating Category: 1U" Gold
 镀层: 1U" Gold
 Wave soldering temperature: 260±5°C, 10S
 波峰焊温度: 260±5°C, 10S

X4622 W V S - 2xXX I - C40 D64 - E60
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: V-Straight 180°
4. Welding Way: S-SMT
5. Row No. Pin No: 2xXX-2x02~2x40P
6. Plastic Height: l=2.0mm
7. Pin Length: C=4.0mm
8. Pin Pitch: D=6.4mm
9. Pin Length: E=6.0mm

X4622WVS-2xXXI-C40D64-E60	PA6T	Brass	X4621F
PART NO	Material	Material(Pin)	Suitable XKB Female

广东星坤科技股份有限公司

Δ姓	日期	ANGLAR	±5°
Δ数		L ≤ 4	±0.2
ΔX		4 < L ≤ 16	±0.3
MARK	DESCRIPTION	16 < L ≤ 63	±0.4
文件工程章	REVISIONS	L > 63	±0.5
		UNSPECIFIED TOLERANCES	



DSND	SCALE: N/A	MODEL TYPE:	2.0mm BTB Connector
DWN	VIEW:	PART NO.:	X4622WVS-2xXXI-C40D64-E60
CHKD	UNIT: mm/in	DWG NO.:	X-X4622WVS-2xXXI-C40D64-E60
APPD	SIZE: A4	WEIGHT	SHEET

XKB INDUSTRIAL PRECISION CO., LIMITED