



P.C.B LAYOUT

■ 规格 Specifications:

- 额定电压 Voltage rating:250VAC/DC.
- 额定电流 Current rating:3A AC/DC
- 耐电压 Withstanding voltage:1000V AC/minute
- 温度区间 Temperature range:-40℃to+105℃
- 绝缘电阻 Insulation resistance:≥1000MΩ Min
- 接触电阻 Contact resistance:≤20MΩ Max
- 材料 Material: PA6T UL94V-0
- 镀层 Planting Category: 1U"Gold
- 回流焊温度 Reflow soldering temperature:260±5℃, 10s

X6521 F R S - 2xXX - C59 D11
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category:F-Female
- ③ Welding Board Angle:R-Sright 90°
- ④ Welding Way S-SMT
- ⑤ Row No -Pin No:2xXX-2x02P-2x40P
- ⑥ Plastic height: C=5.9mm
- ⑦ Plastic length:D=11.0mm

X6521FRS-2xXX-C59D11	PA6T UL94V-0	Brass	1U"Gold	X6521W
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Water

ΔX					ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4
	REVISIONS				L > 63	±0.5
						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



DSND		SCALE: N/A	MODEL TYPE: 2.54mm Crimp Style Connector
DWN		VIEW:	PART NO.: X6521FRS-2xXX-C59D11
CHKD		UNIT: mm/in	DWG NO.: X-X6521FRS-2xXX-C59D11
APPD		SIZE: A4	
		WEIGHT	SHEET
		1/1	REVISION A0

XKB INDUSTRIAL PRECISION CO.,LIMITED