


贴片时正反贴须告知，正反贴生产工艺有区别

* 所有原料材质, 生产制程, 电镀必须符合ROHS要求




1. SPECIFICATIONS
 INSULATION RESISTANCE: 500M min. AT DC 500V DC
 WITHSTANDING VOLTAGE: 250V AC rms FOR 1 MINUTE
 CONTACT RESISTANCE: 100M max. AT 10mA/20mV max
 CURRENT RATING: 0.5A
 VOLTAGE RATING: 5.0 vrms
 OPERATING TEMP. RANGE: -55 C+85 C
 MATING CYCLES: 5000 INSERTIONS

2. MATERIAL:
 INSULATOR: H-TEMPERATURE PLASTIC, UL 94V-0,
 COLOR: BLACK
 TERMINAL: COPPER ALLOY, T=0.15mm
 SHELL: STAINLESS STEEL, T=0.15mm

3. FINISH:
 TERMINAL: 50u* min NICKEL UNDERPLATED ON ALLOVER, GOLD PLATING
 ON CONTACT ARER, 80u*min TIN ON SOLDER TAIL
 SHELL: 50u* NICKEL UNDERPLATED ON ALLOVER, GOLD FLASH ON SOLDER
 LATCH

SIM pin assignment	
PIN#	Name
C1	VCC 电压
C2	RST 重置
C3	CLK 时钟
C4	Reserved 备用
C5	GND 接地
C6	VPP 电压
C7	I/O 输入输出
C8	Reserved 备用



连欣科技
Lian Xin Technology

深圳市连欣科技有限公司

DIMENSIONS INIT: mm UNLESS OTHERWISE SPECIFIABLE DIMENSION TOLERANCE X.X: ± 0.25 X.XX: ± 0.10 X.XXX: ± 0.05 ANGULAR: ± 1°	PRODUCT NAME : SIM PUSH 8P+1P无柱	DRAWING: COCO	DATE: 2012/05/10	
	PRODUCT NO. : XDSM-0863-0111	CHECK: JANY	DATE: 2012/05/10	1:1 P D A 1 of 1
	DRAWING NO. : 0111AAAS06A	APPROVED: JEFF	DATE: 2012/05/10	

REVISION NO.	ECR NO.	DESCRIPTION	MARK	DATE
1				
2				

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作