


NOTE:
 1. MATERIAL:
 a. HOUSING: THERMOPLASTIC GLASS FIBRE UL94V-0
 b. CONTACT: PHOSPHOR BRONZE
 (SURFACE PLATING: NI100u" SN100u" SN100u" 120u")
 SEE ORDERING INFORMATION
 2. ELECTRIC:
 a. CONTACT RESISTANCE: 30 MILLIOHMS MAX
 b. INSULATION RESISTANCE: 1000 MEGA OHMS MAX
 c. DIELECTRIC VOLTAGE: 750V AC ONE SEC LEVEL
 d. OPERATING TEMPERATURE: -55° C ~ +85° C



PCB LAYOUT DIAGRAM
 Top View

TOLERANCE		Tolerance: Unless otherwise specified	
LINEAR	ANGLE		
X	±1	3	TERMINAL-2
±5°	±0.38	2	TERMINAL-1
±2°	±0.25	1	HOUSING
±1°	±0.10		

NO.	PART NAME	MATERIAL	COLOR/FINISH
3	TERMINAL-2	PHOSPHOR BRONZE	Sn-Plated
2	TERMINAL-1	PHOSPHOR BRONZE	Sn-Plated
1	HOUSING	LCP	WHITE

深圳市连欣科技有限公司

www.szlianxinkeji.com/

PART NO: XD CR-2032-604

TITLE:

CR2032-6 贴片电池座带孔 SMT