



**规格:**

1. 插入力: 44.1N MAX.
2. 拔出力: 9.8~25N
3. 耐久性: 10000 CYCLES MIN.
4. 额定电流: 0.5A
5. 额定电压: 40V MAX
6. 耐电压: 500V AC MIN. (UNMATED)  
300V AC MIN. (MATED)
7. 接触阻抗: 30mΩ MAX.
8. 绝缘电阻: 100MΩ MIN (UNMATED)  
10MΩ MIN (MATED)
9. 工作温度: -20°C TO +85°C
10. 所用材质须符合RoHS要求

**L&X 深圳市连欣科技有限公司**

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : <b>陈一鸣</b>	DATE : <b>2014-02-23</b>	PART NAME: <b>HDMI A TYPE 侧插</b>	
	CHECKED BY : <b>马跃</b>	DATE : <b>2014-02-23</b>	PART NO. <b>XDHF-1901-0811</b>	MOLD NO.
UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY : <b>邱国夷</b>	DATE : <b>2014-02-23</b>	DRAW NO.: <b>LX-HDMI16080811</b>	SHEET NO.: <b>1 OF 1</b>