

RoHS

REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.09.05

技术参数(SPECIFICATIONS)

额定电流(Current rating) : 3A
 耐压值(Withstand voltage) : 500V AC
 绝缘电阻(Insulation resistance) : 1000M
 接触电阻(Contact resistance) : 20m
 工作温度(Working temperature) : -40 +105

材料 (MATERIAL)

绝缘体(Insulator Material) : PBT UL 94V-0 Black
 接触材料(Contact Material): Brass
 电镀(Contact Plating) : Gold-Flash





产品名称说明 :

EH254V-12-xxP
 1 2

1.序列号

2.Pin位数:06-64Pin
 06=06

No. of Pins/Row	Dimension	
	A	B
06	5.08	26.82
08	7.62	29.36
10	10.16	31.90
14	15.24	36.98
16	17.78	39.52
20	22.86	44.60
24	27.94	49.68
26	30.48	52.22
30	35.56	57.30
34	40.64	62.38
40	48.26	70.00
50	60.96	82.70
60	73.66	95.40
64	78.74	100.48



P.C.B Hole Layout

X.±0.50	X.°±
.X±0.25	.X°±
.XX± 0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO.: EH254V-12-xxP
 TITLE: 2.54mm牛角180° DIP
 长耳 PC:3.2

APPD:
 CHKD:
 DRAW: Tong.Deng 2023.09.27

XFCN兴飞连接器

0769-82001899
 www.xfconn.com

DWG NO: /		
SCALE	SHEET	REV.
NONE	1/1	A1