



Specifications:

规格:

1. **Voltage rating:** 150VAC/DC
额定电压: 150V AC/DC
2. **Current rating:** 3A AC/DC
额定电流: 3A AC/DC
3. **Withstanding voltage:** 500V AC/minute
耐受电压: 500V AC/分钟
4. **Temperature range:** -25°C~+85°C
温度范围: -25°C~+85°C
5. **Insulation resistance:** 1000MΩ
绝缘电阻: 1000MΩ
6. **Contact resistance:** 20mΩ
接触电阻: 20mΩ
7. **After environmental testing:** 40mΩ
环境测试后: 40mΩ

X1503 W R S- XX XX - 4T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category: W-Water
- ③ Welding Board Angle: R-Stright 90°
- ④ Welding Way S-SMT
- ⑤ Row No -Pin No: XX-02P-12P
- ⑥ Plug the pin&special No
- ⑦ Material: 4T PA4T 94V-0
- ⑧ Planting style: V01-Gold-Flash

Poles	Dimensions(mm)			
	A	B	C	D
02	1.50	6.75	2.85	
03	3.00	8.25	4.35	
04	4.50	9.75	5.85	
05	6.00	11.25	7.35	3.00
06	7.50	12.75	8.85	3.00
07	9.00	14.25	10.35	4.50
08	10.50	15.75	11.85	6.00
09	12.00	17.25	13.35	7.50
10	13.50	18.75	14.85	9.00
11	15.00	20.25	16.35	10.50
12	16.50	21.75	17.85	12.00

X1503WRS-XX-4TV01	PA4T UL94V-0	Brass	Gold-Flash	Brass	Tin	X1503H
PART NO	Material	Material(Pin)	Finish(Pin)	Material()	Finish()	Suitable XRB Housing

DSND		SCALE: N/A	MODEL TYPE: Wire to Board Connector
DWN		VIEW:	PART NO.:
CHKD		UNIT: mm/in	DWG NO.:
APPD		SIZE: A4	X1503WRS-XX-4TV01
			WEIGHT
			SHEET
			REVISION
			1/1
			A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

广东星坤科技股份有限公司

日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED

REVISIONS
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn