

## Specification Sheet

Part Number: 151-01246



HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications. Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.

An assortment of Connector Clips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Conn. Clip w/Oval Fir Tree, 0.51-6.75mm Panel Thick, 6.2-13.0mm Hole, PA66HIRHSUV, Black, 5000/ctn

Article Number 151-01246

Type CCOVAL4

Color Black (BK)

Quantity Per carton

Product Description Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.

Short Description Conn. Clip w/Oval Fir Tree, 0.51-6.75mm Panel Thick, 6.2-13.0mm Hole, PA66HIRHSUV, Black, 5000/ctn

Global Part Name

CCOVAL4-PA66HIRHSUV-BK

Length L (Imperial)

0.93

Length L (Metric)

23.60

Fixation Method

Fir Tree for oval holes

Width W (Imperial)

0.69

Width W (Metric)

17.6

Height H (Imperial)

0.85

Height H (Metric)

21.6

Panel Thickness Min (Imperial)

0.023

Panel Thickness Max (Imperial)

0.27

Panel Thickness Min (Metric)

0.6

Panel Thickness Max (Metric)

6.75

Mounting Hole Diameter D (Imperial)

0.24 x 0.48 " 0.26 x 0.50 " 0.26 x 0.51 " 0.28 x 0.47

Mounting Hole Diameter D (Metric)

6.5 x 12.5 mm 6.2 x 12.2 mm 6.5 x 13.0 mm 7.0 x 12.0 mm

Mounting Hole Diameter D Min (Imperial)

0.24

Mounting Hole Diameter D Max (Imperial)

0.51

Mounting Hole Diameter D Max (Metric)	13.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)