

SAC-8P-15,0-PUR/M 8FR - Sensor/actuator cable



1145453

<https://www.phoenixcontact.com/pc/products/1145453>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 8-position, PUR halogen-free, black-gray RAL 7021, free cable end, on Socket angled M8, cable length: 15 m

Commercial data

Item number	1145453
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	BF1BGA
GTIN	4063151135829
Weight per piece (including packing)	481.55 g
Weight per piece (excluding packing)	481.55 g
Customs tariff number	85444290
Country of origin	PL

SAC-8P-15,0-PUR/M 8FR - Sensor/actuator cable



1145453

<https://www.phoenixcontact.com/pc/products/1145453>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	8

Insulation characteristics

Degree of pollution	3
---------------------	---

Material specifications

Outer sheath, material	PUR
------------------------	-----

Electrical properties

Nominal voltage U_N	30 V AC
	30 V DC
Nominal current I_N	1.5 A

Connection data

Conductor connection

Tightening torque	0.2 Nm
-------------------	--------

Connector

Connection 1

Type	free cable end
------	----------------

Connection 2

Type	Socket angled M8
Number of positions	8
	8

Cable/line

Cable length	15 m
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP68

SAC-8P-15,0-PUR/M 8FR - Sensor/actuator cable





1145453

<https://www.phoenixcontact.com/pc/products/1145453>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1145453>

 UL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	1.5 A	-	-

 cUL Listed Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	1.5 A	-	-

cULus Listed				
---------------------	--	--	--	--

SAC-8P-15,0-PUR/M 8FR - Sensor/actuator cable



1145453

<https://www.phoenixcontact.com/pc/products/1145453>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-8P-15,0-PUR/M 8FR - Sensor/actuator cable



1145453

<https://www.phoenixcontact.com/pc/products/1145453>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com