

GloTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" to IEC320-C7, GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227, 2000mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. 2074112M703A(R)	Rev G

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

In Addition to GlobTek Inc.'s renewed ISO9001:2008 - Quality Management System Certification, GlobTek Inc. is now certified to:

- ISO13485:2003 - Medical Devices Quality Management System Certification
- ISO14001:2004 - Environmental Management System Certification

ISO Certificates are available online at <https://www.globtek.com/iso-certificates/>
Prop 65 Statement: <https://en.globtek.com/prop-65-statement.pdf>

The acceptance of this specification and use of the product described in this document indicates the acceptance and binding of the customer to Globtek TERMS AND CONDITIONS (attached to the end of this document), which supersede all other agreements, terms, and conditions (<https://en.globtek.com/terms-and-conditions/>).

The purchaser of this product (Customer) agrees that it is their sole responsibility to determine suitability/fitness of the product described in this specification for their application and to take precautions for protection against any hazards attendant to the handling and use of the product.

Footnote:

GlobTek Inc. will not be liable for the safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult applicable UL, CSA or EN standards for proper installation instruction.

Limitation of Use:

GlobTek products are intended for use with commercial, medical, and/or industrial equipment only. GlobTek product are not authorized for use as mission critical components in life support hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of GlobTek Inc.
Contents of this document are subject to change without prior notice.

Customer Approval of Specification:

Please approve, sign and send back to GlobTek so we can complete order processing.
A delay in receipt of this form will delay delivery schedule.

Company Name: _____	Customer P/N: _____
Quote Number: _____	Date: _____
Authorized Representative Name: _____	Authorized Representative Signature: _____

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" to IEC320-C7, GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227, 2000mm, GlobTek Black	
	Model No. Power Cord	
Part No./Ordering No. 2074112M703A(R)		Rev G

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

REVISION HISTORY

REV	DESCRIPTION	SUB	DATE	APPROVED
G		jwarn	11/27/2019	QA
E	ADD 'NF' TO CABLE APPROVALS	jsund	08/13/2014	QA

Cordset Information:

CordsetColor:GlobTek Black


Cord Length (mm):2000

NOTES:


GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" to IEC320-C7, GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227, 2000mm, GlobTek Black
	Model No. Power Cord
Part No./Ordering No. 2074112M703A(R)	Rev G

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

END A



END B



SAA is represented by the file number in the format of NSWxxxxxx



GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" to IEC320-C7, GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227, 2000mm, GlobTek Black	
	Model No. Power Cord	Rev G
	Part No./Ordering No. 2074112M703A(R)	

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

End A Code:207 Description:CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" Rating (V):250 Rating (A):2.5 Gender:Male Overmolded:Yes	Cable Code:411-EURO Description:GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227 Color:GlobTek Black Wire Gauge(AWG):0.75 Cond:2 Type:H03VVH2-F Temperature:70° C Amps:10 Volts:300 OD:3.5 ConductorsColors:BLU/BRN	End B Code:703-ENEC-VDE Description:IEC320-C7 Rating (V):250 Rating (A):2.5 Gender:Female Overmolded:Yes
--	--	--

Overall cable rating:2.5A/250V~

Plug Approvals	Cable Approvals	Connector Approvals
----------------	-----------------	---------------------

 ENEC-VDE and EAC	 Euro + SAA	 ENEC-VDE
		 SAA (may be represented by file number only)

AGENCY ONLINE DOCUMENTS	http://en.globtek.com/cordsets/
RoHS/RoHS3 Declaration	https://www.globtek.com/pdf/rohs_cert/01t30000002p7FKAAAY
REACH Declaration	https://www.globtek.com/pdf/iso_certificates/REACH.pdf
Conflict Minerals Declaration	https://www.globtek.com/pdf/conflict-minerals.pdf
Prop 65 Statement	https://en.globtek.com/prop-65-statement.pdf

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" to IEC320-C7, GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227, 2000mm, GlobTek Black	
	Model No. Power Cord	
	Part No./Ordering No. 2074112M703A(R)	Rev G

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

CE.UKCA.Cord


https://globtek.secure.force.com/spec/ec_decl_product_model_family_incl_cord?id=01t30000002p7FK

IPXY rating is based on 3rd party testing and customers should check suitability and test system level IPXY rating before ordering.

GloTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: CEE7 standard sheet XVI (CEE7/16) (Type C) "Europlug" to IEC320-C7, GT Cable #411-EURO: 0.75 / 2 Conductors, 3.5mm OD, H03VVH2-F, 70 Deg.C, 300V, BLU/BRN, Approvals: IEC60227, 2000mm, GlobTek Black	
	Model No. Power Cord	Part No./Ordering No. 2074112M703A(R)
		Rev G

CUSTOMIZED LENGTHS, COLORS, CABLE TYPES, TERMINATIONS/PLUGS/RECEPTACLES AVAILABLE UPON REQUEST. ADDITIONAL PLUG OPTIONS ARE AVAILABLE AT <https://www.globtek.com/connectors/> STANDARD PLUGS AND CONNECTORS CAN BE SEEN ONLINE AT <https://www.globtek.com/connectors/> ACTUAL CONNECTORS, OVERMOLDS, FERRITES MAY VARY SLIGHTLY FROM THE PICTURE BELOW DIMENSIONS ARE IN MM UNLESS SPECIFIED OTHERWISE

Hanking: 125
Description: 125 +/- 25mm
Image:



Notes/Modifications/Customizations (notes in this section supersede the values shown in the standard spec):