



NOTE:

MATERIAL

HOUSING: PA6T/BK UL94V-0
 CONTACT: COOPER NEEDLS.
 CONTACT PLATING: GOLD PLATING.

ELECTRICAL

CURRENT RATING: 3AMP.
 VOLTAGE RATING: 250V AC/DC
 DIELECTRIC WITHSTANDING VOLTAGE: 600V AC/minute.
 CONTACT RESISTANCE: 20mΩMAX.
 INSULATION RESISTANCE: 1000MΩMIN.

ENVIRONMENTAL

TEMPERATURE RANGE: -40° C TO +105° C.

DIMENSION TABLE:

PIN	A(mm)	B(mm)	C(mm)	PIN	A(mm)	B(mm)	C(mm)
2X3	15.22	5.08	12.92	2X10	33.00	22.86	30.70
2X4	17.76	7.62	15.46	2X12	38.08	27.94	35.78
2X5	20.30	10.16	18.00	2X13	40.62	30.48	38.32
2X6	22.84	12.70	20.54	2X15	45.70	35.56	43.40
2X7	25.38	15.24	23.08	2X17	50.78	40.64	48.48
2X8	27.92	17.78	25.62	2X20	58.40	48.26	56.10
2X9	30.46	20.32	28.16	2X25	71.10	60.96	68.80

RoHS2.0

本圖紙知識產權及版權歸深圳市永豐盈電子有限公司所有，未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的權力。

類別	簡牛	品名	CS-1200-XX(L=11.6)	X.	±0.50	材料	單位	mm	SHEET 1 OF 1		
版本	A/1	設計	李文暢	X.X	±0.20	顏色	黑色	比例	修改內容	修改日期	
制定部門	工程部門	繪制		X.XX	±0.10	画法		數量			
工程圖號	CST-1200	審核	李文暢	X.XXX	±0.05	CST 深圳市永豐盈電子有限公司 ShenZhenYongFengYing ELEECTRONICS CO.,LTD.					
制定日期	2019-4-22	核准	周中湖	X.XXXX	±0.02						
