

**■ SPECIFICATIONS**






- Voltage rating: 50V AC, DC
- Current rating: 1A, AC, DC
- Withstanding voltage: 500V AC/minute
- Insulation resistance: 1000M Ω min
- Temperature range: -40°C - +105 ° C
- Contact resistance: 20m Ω max

**■ WAFER**

- Part No. :CS-1254R-XX
- Poles:2-16
- Material: LCP, NATURAL COLOR , UL94V-0
- Contact: C2680, Tin plated
- Q' TY: 1,000 pcs/bag

Poles	PART NO	DIMENSION (mm)	
		A	B
2	CST-1254R-02	1.00	4.00
3	CST-1254R-03	2.00	5.00
4	CST-1254R-04	3.00	6.00
5	CST-1254R-05	4.00	7.00
6	CST-1254R-06	5.00	8.00
7	CST-1254R-07	6.00	9.00
8	CST-1254R-08	7.00	10.00
9	CST-1254R-09	8.00	11.00
10	CST-1254R-10	9.00	12.00
11	CST-1254R-11	10.00	13.00
12	CST-1254R-12	11.00	14.00
13	CST-1254R-13	12.00	15.00
14	CST-1254R-14	13.00	16.00
15	CST-1254R-15	14.00	17.00
16	CST-1254R-16	15.00	18.00

**ROHS 2.0**



本圖紙知識產權及版權由永丰盈有限公司所有,未經書面許可不准擅自傳閱、复制和修改。本公司保留法律追究的权利。

类别	WAFER	品名	CS-1254R-XX	X.	±0.50	材料		单位	mm	SHEET 1 OF 1			
	版本	A/1	设计	李文畅	X.X	±0.30	颜色		比例	1:1	▲1	修改内容	修改日期
	制定部门	工程课	绘制	李文畅	X.XX	±0.20	画法		数量		▲1	加储存方式	2017-08-10
	工程图号	CST-1254R	审核	姚培柱	X.XXX	±0.10	CST 深圳市永丰盈电子有限公司 ShenZhenYongFengYing ELECTRONICS CO.,LTD.				▲2		
	制定日期	2017-11-30	核准	周中湖	X.XXXX	±0.05					▲3		