



■ SPECIFICATIONS

- Voltage rating:250V AC/DC
- Current rating: 2A, AC/DC
- Withstanding Voltage:800V AC/minute
- Insulation resistance:1,000MΩ min
- Temperature range:-40°C to+105 °C
- Contact resistance:20mΩ max

■ WAFER

- Part No:CS-1261R-XX
- Poles:2-16
- Material:LCP UL94V-0
- Pin:Cooper needles(H65),
Tin Plated(镀高温锡)
- Q' TY:1,000 pcs/Tape&reel

ROHS 2.0

本圖紙知識產權及版權由永豐盈電子有限公司所有,未經書面許可不准擅自傳閱、複製和修改.本公司保留法律追究的權利.

SORT	WAFER	PART NO.	CS-1261R-XX	X.	±0.50	MATERIAL		UNIT	mm	SHEET 1 OF 1		
VERSION	A/O	DESIGNER	李文暢	X.X	±0.30	RIGIDITY		SCALE	1:1	⚠	REVISE	REVISE DATE
FRAME	工程課	DRAW BY	李文暢	X.XX	±0.20	PROJECTION	☉	QUANTITY		⚠		
DRAWING NO.	CST-1261R	CHECK BY	YAO PEI ZHU	X.XXX	±0.10					⚠		
DATE	2019-07-23	APPROVE	ZHOU ZHONG HU	X.XXXX	±0.05					⚠		

CST 深圳市永豐盈電子有限公司
ShenZhenYongFengYing ELECTRONICS CO., LTD.