


Product data sheet

Specifications

Cable duct - 90 x 60 mm - without cover - blue



AK2GA69

Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Blue RAL 5000)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	3.54 in (90 mm)
Length	78.74 in (2000 mm)
Width	2.36 in (60 mm)
Net weight	2.65 lb(US) (1.2 kg)
Total number of wires	400

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	NF C 68-102 VDE 0506 VDE 0660 DIN 43659

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Package 1 Height	7.28 in (18.5 cm)
Package 1 Width	5.71 in (14.5 cm)
Package 1 Length	84.65 in (215 cm)
Package 1 Weight	32.31 oz (916 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	7.28 in (18.5 cm)
Package 2 Width	5.71 in (14.5 cm)
Package 2 Length	78.74 in (200 cm)
Package 2 Weight	17.64 lb(US) (8 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	288
Package 3 Height	84.65 in (215 cm)
Package 3 Width	55.12 in (140 cm)
Package 3 Length	35.43 in (90 cm)
Package 3 Weight	1181.68 lb(US) (536 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)