



Product: [8527](#)

Lead Wire, #12 Str TC, PVC Ins, TYPE MW MIL-W-76C-PVC

Request Sample

Product Description

Low Temp Plastic Lead Wire, 12AWG (65x30) Tinned Copper, PVC Insulation, TYPE MW MIL-W-76C-PVC 1000V 80C

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, (Type MW) MIL-W-76C-Low Temp applications
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	12 AWG	65x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.021 in (0.53 mm)	0.128 in (3.25 mm)

Overall Cable Diameter (Nominal):	0.128 in (3.25 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Max. Current
4.32 Ohm/1000ft	Single conductor in free air @ 30°C: 9.0 A

Voltage

UL Voltage Rating
1000 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
80°C	-40°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
1.28 in (32.5 mm)	1.28 in (32.5 mm)

Max. Pull Tension:	64 lbs (29 kg)
Bulk Cable Weight:	24 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Outdoor
Sustainability:	CA Prop 65
Military Compliance:	MIL-W-76C Type MWP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision: Revision Number: 0.453 Revision Date: 01-20-2023

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8527 010100	Black	Reel	100 ft	612825212867	
8527 0101000	Black	Reel	1,000 ft	612825212874	C P
8527 006100	Blue, Light	Reel	100 ft	612825212812	
8527 0061000	Blue, Light	Reel	1,000 ft	612825212829	P
8527 0081000	Gray	Reel	1,000 ft	612825212836	P
8527 005100	Green, Dark	Reel	100 ft	612825212799	
8527 0051000	Green, Dark	Reel	1,000 ft	612825212805	P
8527 003100	Orange	Reel	100 ft	612825212768	
8527 0031000	Orange	Reel	1,000 ft	612825212775	P
8527 002100	Red	Reel	100 ft	612825212744	
8527 0021000	Red	Reel	1,000 ft	612825212751	P
8527 009100	White	Reel	100 ft	612825212843	
8527 0091000	White	Reel	1,000 ft	612825212850	P
8527 0041000	Yellow	Reel	1,000 ft	612825212782	P

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.