

# Duplex Multimode 62.5/125 LSZH Fiber Optic Cable, 1000 ft. Bulk

MODEL NUMBER: N549-01K



#### **Highlights**

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen (LSZH) jacket
- Zip-Cord Style

### **Package Includes**

Carton of 1,000ft Duplex 62.5/125 Multimode cable

#### **Features**

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen jacket
- Zip-Cord Style
- Cable marked every meter
- Temp Range: -20C to +70C
- Suitable for Indoor Use
- 7lb Reel

## **Specifications**

OVERVIEW		
UPC Code	037332142924	
Technology	Multimode	
Optical Mode	OM1	
PHYSICAL		
Cable Jacket Color	Orange	
Connector Color	Orange	
Cable Jacket Material	LSZH	
Cable Jacket Rating	OFNR	
Clad Diameter (microns)	125	



Core Diameter (microns)	62.5
Number of Fibers	2
Cable Length (ft.)	1000
Cable Length (m)	304.88
Cable Length (in.)	12000
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	10.24 x 10.24 x 4.70
Shipping Dimensions (hwd / cm)	26.01 x 26.01 x 11.94
Shipping Weight (lbs.)	6.00
Shipping Weight (kg)	2.72
Fiber Cable Length	304.9M (1000 ft)
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
COMMUNICATIONS	
Attenuation @ 850NM	3.0 dB/km
CONNECTIONS	
Side A - Connector 1	62.5 BULK
Side B - Connector 1	62.5 BULK
FEATURES & SPECIFICATIONS	
Push/Pull Tabs	No
Breakout	No
Trunk	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.