Off-the-Shelf (OTS) Mini-Fit Jr. Overmolded Cable Assemblies

molex

Off-the-Shelf (OTS) Mini-Fit Double-ended, Overmolded Assemblies with strain relief are available in multiple circuit sizes and cable lengths for a rugged signal connection

(4-circuit Version Shown)

Mini-Fit Off-the-Shelf Overmolded Cable Assembly Family

Features and Benefits

Both custom and off-the-shelf assemblies available

Provides quick availability for development and production programs and customized versions for final designs

Positive latching

Ensures secure retention when receptacle and header or receptacle and plug are mated. Prevents accidental unmating



Polarized mating geometry

Prevents mis-mating

Terminal provides 4 independent points of contact

Offers redundant, secondary current paths for long-term electrical performance and reliability

Terminal polarization tab

Ensures the terminals are fully inserted into the plugs and receptacles. Reduces risk of terminal backout

Applications

Consumer

Office equipment

Fan tray assemblies

Gaming and vending

Data/Computing

Personal computers

Computers, work stations and servers



Work Stations



Office Equipment



Gaming Machines



Off-the-Shelf (OTS) Mini-Fit Jr. Overmolded Cable Assemblies



Specifications

Electrical

Voltage (max.): 300V AC/DC Current (max.): 8.4A

Dielectric Withstanding Voltage: 2000V AC Insulation Resistance (min.): 10 Megohms

Mechanical

Insertion Force to PCB (max.): 15N Retention Force (min.): 30.0N Mating Force (max. per circuit): 15.6N Unmating Force (max. per circuit): 13.8N Wire Pullout Force (min.): 89.0N Durability (min.): 100 cycles

Physical

Flammability: UL 94V-2 Housing: Nylon, Natural Terminal: Copper Alloy

Plating: Tin

Wire/Cable: UL2464, Black, 80°C, xC*18AWG, 300V

Overmolding resin: PVC, Black Operating Temperature: -20 to +80°C

Ordering Information

Part No.	Description	Length (m)	Number of Circuits
<u>245135-0205</u>		0.5	
<u>245135-0210</u>		1.0	2
<u>245135-0220</u>		2.0	
<u>245135-0405</u>		0.5	
<u>245135-0410</u>		1.0	4
<u>245135-0420</u>		2.0	
<u>245135-0605</u>		0.5	
<u>245135-0610</u>	OTS Mini-Fit Overmolded Cable Assemblies	1.0	6
<u>245135-0620</u>		2.0	
<u>245135-0805</u>		0.5	
<u>245135-0810</u>		1.0	8
<u>245135-0820</u>		2.0	
<u>245135-1005</u>		0.5	
<u>245135-1010</u>		1.0	10
<u>245135-1020</u>		2.0	

Custom Product	Description	
Contact Molex	Mini-Fit Jr. Off-the-Shelf Overmolded Cable Assemblies	

www.molex.com/link/overmolded.html