

ITEM	PART#	DESCRIPTION	QTY	UOM
A	5055700201	2.0W/B SINGLE REC HSG 2CKT BLK	1	PC
B	5055721000	2.0W/B REC CRIMP TERM CHAIN H>F	2	PC
C	--	PAPER PRINTED PAPER WHITE	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	--	1X22AWG DISC SR-PVC BK UL10002	BLACK




TABLE			
PART NUMBER	L1	L2(REF)	TITLE
2181021020	50±3	12	MICROLOCK PLUS 2.0 RS 2CKT 50MM DISC Sn
2181021021	100±5	37	MICROLOCK PLUS 2.0 RS 2CKT 100MM DISC Sn
2181021022	150±8	62	MICROLOCK PLUS 2.0 RS 2CKT 150MM DISC Sn
2181021023	300±10	137	MICROLOCK PLUS 2.0 RS 2CKT 300MM DISC Sn
2181021024	600±10	287	MICROLOCK PLUS 2.0 RS 2CKT 600MM DISC Sn

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2021/03/12	A	INITIAL RELEASE	AS20

- NOTES**
- CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1MM. TINNING DIA MUST BE 0.9MM MAX.
 - LABEL TEXT MUST BE 2MM MAX IN HEIGHT WITH ARIAL FONT.
 - LABEL MUST BE WRAPPED IN FLAG TYPE.

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		
	$\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$	DIMENSION UNITS: mm SCALE: NTS	EC NO: 665161 DRWN: AS20 CHK'D: RDESAI01 APPR: RDESAI01		
DIVISIONAL SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±	INITIAL REVISION: DRWN: AS20 APPR: RDESAI01		PRODUCT CUSTOMER DRAWING	DOCUMENT NUMBER: 2181021020 DOC TYPE: PSD DOC PART: 000 REVISION: A
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING: A4-SIZE	SERIES: 218102	MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 1 OF 1