


Specification Sheet

Part Number: 157-00295



Covers top of stud for protection from stud end.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

PA46 material option allows use in high-heat applications.

M12 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA46, Brown, 2000/pkg

Article Number 157-00295

Type T80ROSSB12U

Color Brown (BN)

Quantity Per carton

Product Description Stud Mount Ties offer outstanding stud retention. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description M12 Stud Mount Tie, 7.5" Tie, 80lb Tensile Strength, PA46, Brown, 2000/pkg

Global Part Name T80ROSSB12U-PA46-BN

Minimum Tensile Strength (Imperial)	80.0
Minimum Tensile Strength (Metric)	355
Length L (Imperial)	8.6
Length L (Metric)	218.0
Fixation Method	Stud Mount
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Width W (Imperial)	0.93
Width W (Metric)	23.75
Bundle Diameter Min (Imperial)	0.14
Bundle Diameter Min (Metric)	3.5
Bundle Diameter Max (Imperial)	1.97
Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00295
Height H (Imperial)	0.70

Height H (Metric)	17.0
Mounting Hole Diameter D (Imperial)	0.47" x 0.07
Mounting Hole Diameter D (Metric)	M12 x 1.75
Stud Diameter (Metric)	12.0 mm
Stud Diameter (Imperial)	0.47
Material	Polyamide 4.6 (PA46)
Material Shortcut	PA46
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +266°F (-40°C to +130°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)