



Plug Component			Plug Strip Dimension			Wire Spec.	Terminal ROJ & Strip			Terminal Component		
Color	Component	Qty	Strip	ROJ	Color		Strip	ROJ	Color	Component	Color	Qty
40P Black 90±5°A	LT-550(20A 250V) (IEC 320 C20)	1	6±1	25±3	Black	SJT 12AWGX3C 105°C BLACK  Length: 1219±50 mm	5±1	18±3	Black	LT-549(20A 250V) (IEC 320 C19)	40P BK 90±5°A	1
BLACK	(550 Inner Body)	1	6±1	25±3	White		5±1	18±3	White	terminals	Phosphor bronze	3
Nickel-Plated	2*5 Inlet Blades	2	6±1	25±3	Green		5±1	18±3	Green	(549 Inner Body)	BLACK	1
Nickel-Plated	2*6 Inlet Blades	1										

**NOTE :**

1. PLUG : LT-550 AMERICAN TYPE
2. CONNECTOR : LT-549 IEC-60320 C19
3. CORD : SJT 12AWGX3C 105°C BLACK 4FT
4. APPROVALS : UL, C-UL
5. Supplier for flexible cord : RHYTHM
6. Hi-Pot Test:2000v/1min<1mA>

**Marking:**

RHYTHM: (UL) E88231 SJT 3X12AWG(3.13mm)  
105°C 300V VW-1 CSA LL54496 SJT  
3X12AWG(3.13mm)105°C 300V VW-1  
RHYTHM R

**Modification History**

NO.	DESCRIPTION	DATE

<b>DRAWER</b>	Eric	<b>DATE</b>	20/08/31	<b>P/N</b>	800-12-32D-BL-0004F-1
<b>APPROVE</b>		<b>REV.</b>	0	<b>Dr.No.</b>	1090755
		<b>TOL.</b>			±5mm
		<b>ALL DIMENSIONS IN mm</b>			
		比例			

**CnC Tech**  
Industrial Cable and Connector Technology