

6 5 4 3 2 1

APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/22/22	
A		UPDATE TITLE	7/18/22	JJ/RC
B		ADDED COLOR	8/4/22	LH/RC
C		ADDED PAGE2	9/26/22	WX/RC

LENGTH  
(See Ordering Code)

D

**Product Dimensions**

Part Number	Size		As supplied (mm)		After recovered (mm)			Standard Length (Meter)
	mm	Inch	I.D.(min) (D)	W.T. (Nominal Size) (W)	I.D.(max) (d)	W.T. (w)	Adhesive thickness	
Shrink ratio 4:1								
HST-A-040-XX-X-SR41	4	3/16	4.0	0.40	1.0	1.00±0.28	0.45±0.10	1.22
HST-A-080-XX-X-SR41	8	5/16	8.0	0.45	2.0	1.00±0.28	0.50±0.10	1.22
HST-A-120-XX-X-SR41	12	1/2	12.0	0.45	3.0	1.40±0.28	0.60±0.10	1.22
HST-A-160-XX-X-SR41	16	5/8	16.0	0.55	4.0	1.78±0.38	0.76±0.15	1.22
HST-A-240-XX-X-SR41	24	1	24.0	0.65	6.0	2.25±0.55	0.76±0.15	1.22
HST-A-320-XX-X-SR41	32	1 1/4	32.0	0.70	8.0	2.54±0.55	1.00±0.20	1.22
HST-A-500-XX-X-SR41	50	2	50.0	0.70	13.0	2.54±0.55	1.00±0.20	1.22

W  
D  
d  
w

BEFORE SHRINKING      AFTER SHRINKING

HST-A-XXX-XX-X-SR41

TYPE SEE CHART

Length
4 = 4FT(48"inch)

Color
BK=Black (Stocked)
WT=White (Special Order)
RD=Red (Special Order)
BU=Blue (Special Order)
YW=Yellow (Special Order)
GN=Green (Special Order)

SPECIFICATIONS:  
 Material: Polyolefin  
 Electrical:  
 Shrinkage: 4:1  
 UL Style: UL224, 125°C VW-1 600V  
 Temperature Rating:  
 Operating temperature: -45°C to +110°C  
 Environmental:  
 Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED			<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
DRAWN	LH	6/22/22	TITLE DUAL WALL ADHESIVE LINED HEAT SHRINK TUBING, FLAME RETARDANT POLYOLEFIN	
CHECKED	RC	6/22/22		
APPROVED				
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH			SIZE X	PART NO. HST-A-XXX-XX-X-SR41
REF: -		SCALE: NTS	REV. C	
		SHEET 1	OF 2	

6 5 4 3 2 1

6

5

4

3

2

1



APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-----	-------	-------------	------	------

SEE SHT 1 OF 2 FOR REVISION

CARTON



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN	LH	6/22/22
CHECKED	RC	6/22/22
APPROVED		

**ADAM TECH** 909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

TITLE	DUAL WALL ADHESIVE LINED HEAT SHRINK TUBING, FLAME RETARDANT POLYOLEFIN		
SIZE	PART NO.	REV.	
X	HST-A-XXX-XX-X-SR41	C	
REF:	-	SCALE: NTS	SHEET 2 OF 2

6

5

4

3

2

1

D

D

C

C

B

B

A

A