

Toslink Digital Optical SPDIF Audio Cable, 4M (13.12 ft.)

MODEL NUMBER: A102-04M



Highlights

- Superior-grade optical fiber and precision polished optical terminations
- Best possible sound quality through digital fiber optic signals
- Immune to all forms of EMI/RFI

System Requirements

- Home Theater or Stereo equipment with Toslink capabilities

Package Includes

- 4-meter Toslink Digital Optical Audio Cable

Features

- Digital Optical Fiber offers the best in Audio clarity
- Precision polished optical termination minimizes loss for better high frequencies, and a more realistic stereo image
- Ultra flexible PVC jacket construction makes installation easy, even in hard to reach areas
- Immune to all Electromagnetic and Radio-Frequency interference
- Eliminates distortion caused by inductance, capacitance, and resistance found in copper cables

Specifications

OVERVIEW	
UPC Code	037332121929
Technology	Toslink/SPDIF; Stereo Audio
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	13.1
Cable Length (m)	3.99
Shipping Dimensions (hwd / in.)	0.10 x 5.00 x 7.20
Shipping Dimensions (hwd / cm)	0.25 x 12.70 x 18.29

Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
CONNECTIONS	
Side A - Connector 1	TOSLINK (MALE)
Side B - Connector 1	TOSLINK (MALE)
Latching or Gripping Connector	No
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty