



| | | | |
|----|------|------|----|
| 版本 | 变更内容 | 工程确认 | 日期 |
| | | | |

A





SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperature Range: -25°C~+85°C
- 4、Contact Resistance: 20MΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer Nylon46、UL94V-0
PIN Brass Tin-plated
Solder tad Brass Tin-plated

B

C



| 编号 | 尺寸 (mm) | |
|-----------------|---------|-------|
| | A | B |
| YTC-A1251-02ABW | 1.25 | 7.35 |
| YTC-A1251-03ABW | 2.50 | 8.60 |
| YTC-A1251-04ABW | 3.75 | 9.85 |
| YTC-A1251-05ABW | 5.00 | 11.10 |
| YTC-A1251-06ABW | 6.25 | 12.36 |
| YTC-A1251-07ABW | 7.50 | 13.60 |
| YTC-A1251-08ABW | 8.75 | 14.85 |
| YTC-A1251-09ABW | 10.00 | 16.10 |
| YTC-A1251-10ABW | 11.25 | 17.35 |
| YTC-A1251-11ABW | 12.50 | 18.60 |
| YTC-A1251-12ABW | 13.75 | 19.85 |
| YTC-A1251-20ABW | 23.75 | 29.85 |

PCB LAYOUT

D

E

F

| | | | |
|--|-------------------------|---------------|---------------|
| 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD | 页码 (SHEET) | 1/1 | 单位 (UNIT): MM |
| | 版本 (REV) | A1 | 比例 (SCALE) |
| 品名 (ITEM NO) | 1.25间距卧贴 WAFER DIP TYPE | 日期 (DATE) | 2021. 10. 12 |
| 料号 (PART NO) | YTC-A1251-**-ABW | 设计 (DESIGN) | LUO |
| 图号 (DWG NO) | | 审核 (CHECKED) | ROGER LI |
| | | 核准 (APPROVED) | ROC ZHAO |

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com