


版本 REV.	设变内容 MODIFICATION	日期 DATE	修改 DRAW	核准 APPROVE
A0	NEW	09.04.27		



NOTE:

1.ELECTRICAL:

- 1.1 CONTACT RESISTANCE : 30 MILLIOHMS MAX.
- 1.2 DIELECTRIC WITHSTANDING VOLTAGE : 500 VAC FOR 1 MINUTE.
- 1.3 INSULATION RESISTANCE : 1000 MEGAOHMS MIN.

2. MECHANICAL:

- 2.1 MATING FORCE: 3.5kg MAX.
UNMATING FORCE: 1.02kg MIN.
- 2.2 DURABILITY : 5000 CYCLES

3. ENVIROMENTAL:

OPERARION TEMPERATURE : -40°C~+105°C

ORDER INFORMATION:

UB 009 M L - X P 1
① ② ③ ④ ⑤ ⑥ ⑦

- 1. SERES NO.
USB
- 2. NUMBER OF CONTACTS
005: 9 POSITIONS
- 3. CONNECTING TYPES:
F: FEMALE M: MALE
- 4. BASE COLOR CODE
W: WITER B: BLACK L: BLUE
- 5. CONTACT FINISH
1: SELECTIVE3 1u" COLD PLATED OVER NICKL
3: SELECTIVE3 3u" COLD PLATED OVER NICKL
15: SELECTIVE3 15u" COLD PLATED OVER NICKL
- 6. PACKING
T: TRAY B: TUBE R: RELL P: PAG
- 7. SUFFIX NO.

3	CONTACT	BRONZE	SEE ORDER INFORMATION		制图 DRAWN	Jeremy	单位 UNIT	mm	TOLERANCE UNLESS OTHERWISE SPECIFIED		HJ-Tech 东莞市皇捷通讯科技有限公司 手机: 15015282131 手机: 13714786106	
2	HOUSING	LCP			审核 CHECKED		比例 SCALE	1:1	.X±0.35	.X'±3"		
1	SHELL	BRONZE	NICKLE PLATING 60 u" MIN.		张数 SHEET		1/1	.XX±0.25	.X'±1"	品名 TITLE	USB 3.0 AM 焊线短体成品	
项次 NO.	品名 NAME	材质 MATERIAL	表面处理 PLATING	备注 REMARK	核准 APPROVE		角法 PROJ.	①	.XXX±0.10	.XX'±	图号 DWG NO.	2LS00P0008