



PCB LAYOUT

版本	变更内容	工程确认	日期

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 125V AC, DC
- 3、Temperature Range: -25°C~+85°C
- 4、Contact Resistance: 20MΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer PBT、UL94V-0  
PIN Brass Tin-plated

编号	尺寸 (mm)	
	A	B
YTC-A1251-S-02A	1.25	4.25
YTC-A1251-S-03A	2.50	5.50
YTC-A1251-S-04A	3.75	6.75
YTC-A1251-S-05A	5.00	8.00
YTC-A1251-S-06A	6.25	9.25
YTC-A1251-S-07A	7.50	10.50
YTC-A1251-S-08A	8.75	11.75
YTC-A1251-S-09A	10.00	13.00
YTC-A1251-S-10A	11.25	14.25
YTC-A1251-S-11A	12.50	15.50
YTC-A1251-S-12A	13.75	16.75
YTC-A1251-S-20A	23.75	26.75

<b>深圳市怡远科技有限公司</b> SHENZHEN YIYUAN TECHNOLOGY CO., LTD	页码 (SHEET)	1/1	单位 (UNIT): MM
	版本 (REV)	A1	比例 (SCALE)
品名 (ITEM NO)	1.25间距闭口直针 WAFER DIP TYPE	日期 (DATE)	2021. 10. 12
料号 (PART NO)	YTC-A1251-S-**A	设计 (DESIGN)	LUO
图号 (DWG NO)		审核 (CHECKED)	ROGER LI
		核准 (APPROVED)	ROC ZHAO

These drawings and specifications are Shenzhen Yiyuan Technology Co Ltd. The property should not be copied. Without Shenzhen Yiyuan Technology Co. Ltd. Prior written consent to copy or use in any way. Email at info@yiyuanswitches.com